




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED AS PER ECR-15-005925	21APR2015	RS	JL
	A1	REVISED AS PER ECR-15-009215	19JUN2015	RS	JL

NOTES:

- 1 MATERIALS:
CONTACTS: COPPER ALLOY, TIN PLATE
CONTACT POSITIONER: GLASS FILLED PBT,
COLOR BLACK.
2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)
3. CONTACTS (3X) ARE PRE-ASSEMBLED INTO CONTACT
POSITIONER AS SHOWN.
- 4 ASSEMBLY "KEY" ALIGNS WITH "PE"
CONTACT AS SHOWN.
5. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING



IEC (DEKRA)	1-2213427-1
UL	2213427-1
AGENCY APPROVALS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHAFFER 31MAR2014	TE Connectivity		
		CHK M. LUKSIC 31MAR2014			
		APVD M. LUKSIC 31MAR2014	NAME ASSY, FI SOCKET, NECTOR M-LINE SEALED, 3 POSN		
DIMENSIONS: mm		PRODUCT SPEC 108-133014	SIZE A3		
		APPLICATION SPEC 114-32111	CAGE CODE -		
MATERIAL -		WEIGHT -	DRAWING NO C-2213427		
		Customer Drawing	RESTRICTED TO -		
			SCALE 1:1		
			SHEET 1 OF 1		
			REV A1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2213427-1](#)