


P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REVISED PER ECO-17-015513	19DEC2017	PHM	CT



1. CONNECTOR DIMENSIONS ARE PER ARINC 600 SPECIFICATION
- 2 KEYING SHOWN IN POSITION "01" FOR REFERENCE ONLY. CONNECTORS SHIPPED WITH KEYING INSTALLED IN POSITION PER TABLE FOR POSITION "00" KEYING SHIPPED UNASSEMBLED.
- 3 O-RING LUBRICATED WITH PARKER SUPER O-RING-LUBE OR ENGINEERING APPROVED EQUIVALENT.

COMPONENT	MATERIAL	FINISH
SHELL	DIE CAST ALUMINUM PER ASTM-B-85	ELECTROLESS NICKEL PER MIL-C-26074
RETENTION PLATES	ALUMINUM ALLOY PER ASTM-B-209	ELECTROLESS NICKEL PER MIL-C-26074
SCREWS	STEEL OR STAINLESS STEEL	PASSIVATED
POLARIZING POSTS	ZINC ALLOY PER ASTM-B-86	ELECTROLESS NICKEL PER MIL-C-26074
INSERTS	THERMOSET	—
EMI GROUND SPRING	BERYLIUM COPPER 172 (ALLOY 29)	ELECTRODEPOSITED NICKEL PER QQ-N-290
GROMMET	FLUOROSILICONE	—
POLARIZING POST RETAINING PLATE	ALUMINUM ALLOY PER ASTM-B-209	BLUE ANODIZED PER MIL-A-8625

"00"	MODULE A 208267-2 (SIZE 20 SOCKET CONTACT; QTY=60)	2221548-1
	MODULE B 208267-2 (SIZE 20 SOCKET CONTACT; QTY=60)	
	MODULE C 208262-3 (SIZE 22 PIN CONTACT; QTY=100)	
KEYING POSITION	CONTACTS INCLUDED NOT INSTALLED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 11-9-12	 TE Connectivity	
DIMENSIONS: INCHES		CHK W.BERNHART 11-9-12		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD W.BERNHART 11-9-12	NAME	
	0 PLC ± .005	PRODUCT SPEC	PLUG ASSY, SIZE 2, ARINC 600, (60/60/100)	
	1 PLC ± .005	APPLICATION SPEC	—	
	2 PLC ± .005	—	—	
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT	SIZE A1	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO 2221548	RESTRICTED TO —
		SCALE 3:2	SHEET 1 of 1	REV C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2221548-1](#)