




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	22JAN2016	NK	RH



- 1
- WORKING TEMPERATURE: 105° C
- 2
- VOLTAGE: 300V MAX.
- 3
- COLOR: GREY
- 4
- WIRE RANGE: #22-#14AWG MAX.1#16
W/1#18 W/1#20 MIN.2#22
- 5
- SPRING INSERT: STEEL

2299502-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K	22JAN2016	 TE Connectivity			
		CHK HILL RYAN	22JAN2016				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD HILL RYAN	22JAN2016	NAME			
	0 PLC ± —	PRODUCT SPEC	CPGI—WC—WG—GR—BULK				
	1 PLC ± 0.2[.007]	—					
	2 PLC ± 0.4[.015]	APPLICATION SPEC					
	3 PLC ± —	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
	4 PLC ± —	—	A3	00779	C-2299502	—	
	ANGLES ± —	WEIGHT —					
MATERIAL TOUGH THERMOPLASTIC UL 94V-2 FLAME-RETARDANT	FINISH —	CUSTOMER DRAWING			SCALE 3:1	SHEET 1 OF 1	REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2299502-1](#)