





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	13JAN2016	NK	RH



- 1
- WORKING TEMPERATURE: 105° C
- 2
- VOLTAGE: 600V MAX.
- 3
- COLOR: YELLOW
- 4
- WIRE RANGE: #22-#10AWG MAX.3#12 MIN.4#22
- 5
- SPRING INSERT: STEEL

2299513-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 13JAN2016	 TE Connectivity			
		CHK HILL RYAN 13JAN2016				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD HILL RYAN 13JAN2016	NAME			
	0 PLC ± -	PRODUCT SPEC	CPGI-WC-CG-YW-BULK			
	1 PLC ± 0.2[.007]	—				
	2 PLC ± 0.4[.015]	APPLICATION SPEC				
	3 PLC ± -	—				
4 PLC ± -	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
MATERIAL	FINISH	WEIGHT	A3	00779	C-2299513	—
UL 94V-2 FLAME-RETARDANT THERMOPLASTIC SHELL	—	CUSTOMER DRAWING			SCALE	3:1
					SHEET	1 OF 1
					REV	A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2299513-1](#)