






INSULATOR:PA9T+G.F UL94V-O
CONTACT:PHOSPHOR BRONZE
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDER TAIL
50u" NICKEL UNDERPLATED OVERALL

HOLDDOWN:BRASS,100u" TIN OVER 50u" NICKEL
SHEEL:SPCC,50u" NICKEL PLATING OVERALL
RIVET:BRASS,NICKEL PLATING OVERALL
SCREWLOCK:BRASS,Ni PLATED

— STANDS FOR CALENDAR YEAR
— STANDS FOR WEEK NUMBER



3.18 [0.13]	300U BLUE	NO SEE DETAIL Z	30μ"Au	2311586-5
3.18 [0.13]	300U BLUE	NO SEE DETAIL Z	Au Flash	2311586-4
2.7 [0.11]	BLACK	YES	15μ"Au	2311586-3
2.7 [0.11]	661C BLUE	YES	Au Flash	2311586-2
3.18 [0.13]	300U BLUE	YES	Au Flash	2311586-1
X ± 0.38 [± 0.015] POST LENGTH	HOUSING COLOR	SCREWLOCK	Contact Area Plating	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 20FEB2017 CHK DANIEL GORENC 20FEB2017 APVD DANIEL GORENC 20FEB2017		 TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMPLIMITE RECEPTACLE, HD22, RIGHT ANGLE, 15P			
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-130023		APPLICATION SPEC -	
MATERIAL -		FINISH -		WEIGHT -		SIZE A2	
				CAGE CODE 00779		DRAWING NO C-2311586	
						RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 3:1		SHEET 1 OF 1	
						REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2311586-2](#)