






NOTES:

INSULATOR:PA9T+G.F UL94V-O BLACK
CONTACT:PHOSPHOR BRONZE
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDER TAIL
50u" NICKEL UNDERPLATED OVERALL
HOLD DOWN:BRASS,100u" TIN OVER 50u" NICKEL
SHEEL:SPCC,50u" NICKEL PLATING OVERALL
SCREW LOCK:BRASS,30u" NICKEL PLATING OVERALL

LOT NUMBER "XXXX"

— STANDS FOR CALENDAR YEAR
— STANDS FOR WEEK NUMBER

RECOMMENDED P.C.B LAYOUT(TOP SIDE)
(PCB BOARD TOLERANCE ± 0.05)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI CHK 03MAR2017		 TE Connectivity			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD GORENC, DANIEL L 03MAR2017		AMPLIMITE RECEPTACLE, HD22, RIGHT ANGLE, 15P			
		PRODUCT SPEC 108-130023		-			
		APPLICATION SPEC -		-			
MATERIAL -		FINISH -		SIZE A2	CAGE CODE 00779	DRAWING NO C-2311763	RESTRICTED TO -
CUSTOMER DRAWING				SCALE 1:1	SHEET 1 of 1	REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2311763-2](#)