





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E		REVISED PER ECO-19-007626	12SEP2019	AP	DG



NOTES:

Housing:PBT+30%GF(UL94V-0) BLACK
Contact:Brass
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDER TAIL
50u" NICKEL UNDERPLATED OVERALL
Holddown:Brass,100u" TIN OVER 50u" NICKEL
Shell:Cold Roller Steel,Ni Plated
Revitlock:Brass,Nickel Plating
LOT NUMBER "XXXX"
—Stands For Calendar Year
—Stands For Week Number

THREADED	30μAu	2311773-1
-	Contact Area	P/N
	Plating	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI CHK DANIEL GORENC	10MAR2017 10MAR2017	 TE Connectivity	
DIMENSIONS:		APVD DANIEL GORENC	10MAR2017	NAME AMPLIMITE PLUG, HD22, RIGHT ANGLE, 62P,Threaded	
mm	TOLERANCES (UNLESS OTHERWISE SPECIFIED):	PRODUCT SPEC 108-130023		—	
	0 PLC ± — 1 PLC ± — 2 PLC ± 0.25 3 PLC ± — 4 PLC ± — ANGLES ± ± —	APPLICATION SPEC		—	
MATERIAL —	FINISH —	WEIGHT		RESTRICTED TO	
		CUSTOMER DRAWING		SCALE 1:1 SHEET 1 OF 1 REV E	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2311773-1](#)