




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REL PER ECO-18-012662	08AUG2018	JM	RB
	A1	REV PER ECO-18-016694	18OCT2018	JM	RB




2320926-2
SCALE 2:1
KEY B



2320926-3
SCALE 2:1
KEY C



2320926-4
SCALE 2:1
KEY D



COMPANY LOGO

SCALE 2:1

1 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: GRAY

2 MATERIAL: 15% FIBERGLASS REINFORCED PBT
COLOR: (SEE TABLE)

3 MATERIAL: SILICONE
COLOR: LT GRAY.

4. RECOMMENDED WIRE DIAMETER RANGE IS 1.30 TO 2.54mm.

5. RECOMMENDED BACKSHELLS:

STRAIGHT EXIT

- A. 2292860-1 SMOOTH WIRE EXIT
B. 2292860-2 NC12/NW10 CONDUIT WIRE EXIT
C. 2292860-3 NC08/NW7.5 CONDUIT WIRE EXIT


90° EXIT

- D. 2302481-1 SMOOTH WIRE EXIT
E. 2302481-2 NC12/NW10 CONDUIT WIRE EXIT
F. 2302481-3 NC08/NW7.5 CONDUIT WIRE EXIT


6. RECOMMENDED SEAL PLUG: 776363-1.

7. MATING CONNECTOR: 2320932-X.


ORANGE	2320926-4
PURPLE	2320926-3
BLUE	2320926-2
TAN	2320926-1
TPA COLOR	PART NUMBER



2320926-1 SHOWN
KEY A



SECTION A-A



SECTION A-A
WITH TPA IN CLOSED POSITION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J MCNEAL 09OCT2017	TE Connectivity			
DIMENSIONS:		CHK R BALTER 09OCT2017				
mm		APVD R BALTER 09OCT2017	NAME			
		PRODUCT SPEC	CAP ASSEMBLY, 2 POSITION, REDUCED DIA SEAL, HIGH TEMP, AMPSEAL 16			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-2184				
0 PLC ±		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO			
1 PLC ±		114-13065	A200779C-2320926			
2 PLC ±0.30		WEIGHT	RESTRICTED TO			
3 PLC ±		9g	-			
4 PLC ±		Customer Drawing	SCALE 4:1 SHEET OF REV A1			
ANGLES						
FINISH						
MATERIAL						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2320926-1](#)