




1.MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0),COLOR:BLACK
CONTACT:COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY

2.FINISH(ALL OVER):NICKEL PL. 1.27µmMIN
3.FINISH(ALL OVER):TIN PLATED 1.0µmMIN AFTER 2

4.THE SHAPE, SIZE AND POSITION OF THE
CHARACTER SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.
5.THE KEYING ARRANGEMENT OF "Y" IS
SYMMETRIC WITH "X".

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL	19MAR2018	F.Z	R.B
B		REVISED	10AUG2018	F.Z	R.B
B1		REVISED	05FEB2021	F.Z	R.B


RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

40	X	19	38.0	41.0	42.6	TIN PLATED	1-2329463-0
34	Y	16	32.0	35.0	36.6	TIN PLATED	2-2329463-7
34	X	16	32.0	35.0	36.6	TIN PLATED	1-2329463-7
32	X	15	30.0	33.0	34.6	TIN PLATED	1-2329463-6
30	X	14	28.0	31.0	32.6	TIN PLATED	1-2329463-5
28	X	13	26.0	29.0	30.6	TIN PLATED	1-2329463-4
26	X	12	24.0	27.0	28.6	TIN PLATED	1-2329463-3
24	X	11	22.0	25.0	26.6	TIN PLATED	1-2329463-2
22	X	10	20.0	23.0	24.6	TIN PLATED	1-2329463-1
POS	KEY	n	A	B	C	FINISHED	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER ZHU CHK RICK BIAN APVD RICK BIAN	08MAR2018 08MAR2018 08MAR2018	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3, ±3°		NAME DYNAMIC D1100 HEADER ASSY V-TYPE, TIN PLATED, 22~40POS	
MATERIAL 1		APPLICATION SPEC 108-78298 114-5377		RESTRICTED TO -	
FINISH 2-3		WEIGHT		DRAWING NO A200779C-2329463	
		INTERFACE DRAWING		SCALE 2:1 SHEET 1 OF 2 REV B1	

34POS(X-KEY):1-2329463-7

34POS(Y KEY:2-2329463-7)
SYMMETRY FOR KEY ARRANGEMENT



C

B

2 X n = A

16

X

1

STE

D1100

22POS(X-KEY): I-2329463-1

26POS(X-KEY): I-2329463-3

28POS(X-KEY): I-2329463-4

32POS(X-KEY): I-2329463-6

THIS DRAWING IS A CONTROLLED DOCUMENT

DIMENSIONS: mm

MATERIAL

TO TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC ±.5

2. PLC ±0.13

3. PLC ±0.013

4. PLC ±0.0001

ANGLES

FINISH

DWN 08MAR2018 FISHER ZHU

CHK 08MAR2018 RICK BIAN

APVD 08MAR2018 RICK BIAN

PRODUCT SPEC 108-78298

APPLICATION SPEC 114-5377

WEIGHT -

INTERFACE DRAWING

NAME DYNAMIC D1100 HEADER ASSY V-TYPE, TIN PLATED, 22~40POS

SIZE A2

CAGE CODE 00779

DRAWING NO C-2329463

RESTRICTED TO -

SCALE 2:1

SHEET 2 OF 2

REV B1

TE Connectivity

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2329463-6](#)