




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-18-004355	19JUN2018	BDA	SG

- 1 MATERIAL:  
HOUSING- NYLON, 4/6, HIGH TEMP, BLACK.  
CONTACT- COPPER ALLOY  
CAVITY CARRIER TAPE- BLACK CONDUCTIVE PLOYCARBONATE
- 2 FINISH:  
CONTACT - TIN PLATE
- 3 POST TO WITHSTAND 13 NEWTONS [ 3 LBS ] MIN AXIAL FORCE IN THIS DIRECTION WITHOUT DISLODGING, BEFORE SOLDERING.
- 4 POSTS SOLDERTAILS MUST COMPLY WITH TE SOLDERABILITY SPEC 109-11-2.
- 5 MEASURED AT -A-
- 6 APPLIES WHEN HEADER IS HELD STRAIGHT
- 7 COORDINATE DIM APPLIES FROM CENTER OF ACTUAL FEATURE.
- 8 DIMENSION APPLY TO THE COMPONENT SIDE OF BOARD
- 9 MAX TEMP EXPOSURE DURING REFLOW SOLDERING MAY NOT EXCEED 280°C [ 536°F].
- 10 HEADERS ARE SUPPLIED ON A 330.2mm [13] DIAMETER REEL WITH 225 PARTS PER REEL. THE CAVITY CARRIER TAPE HOLDS 1 PART PER POCKET, ORIENTED AS SHOWN.
- 11 TE LOGO, UL AND CSA TRADEMARKS MARKED AT THIS LOACTION



VIEW B-B



1.26 [32MM]	1 REQ'D	1 REQ'D	4	2331450-4
1.26 [32MM]	1 REQ'D	1 REQ'D	3	2331450-3
.945 [24MM]	1 REQ'D	1 REQ'D	2	2331450-2
DIM A	PICK AND PLACE COVER	HEADER ASSEMBLY	NO. OF POSITIONS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BASVESH WARAD 01MAR2018	TE Connectivity	
DIMENSIONS: INCHES		CHK GUERRIERO, SHAYNIA 01MAR2018		
		APVD GUERRIERO, SHAYNIA 01MAR2018	NAME MTA100 HDR ASSY,SM,FL,SN, HT, T&R	
		PRODUCT SPEC	-	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .015 4 PLC ± - ANGLES ± 1°		APPLICATION SPEC	-	
		WEIGHT	-	
MATERIAL -		FINISH -	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-2331450	RESTRICTED TO -
		SCALE 3:1	SHEET 1 OF 3	REV A1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION






COPYRIGHT

By


ALL RIGHTS RESERVED.

## REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



MTA-100 4P HEADER SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BASVESH WARAD 01MAR2018	TE Connectivity	
		CHK GUERRIERO, SHAYNIA 01MAR2018		
DIMENSIONS: INCHES		APVD GUERRIERO, SHAYNIA 01MAR2018	NAME MTA100 HDR ASSY,SM,FL,SN, HT, T&R	
		PRODUCT SPEC	SIZE	
		APPLICATION SPEC	CAGE CODE	
MATERIAL		WEIGHT	DRAWING NO	
FINISH		CUSTOMER DRAWING	RESTRICTED TO	
		SCALE 5:1	SHEET 2 OF 3	
		REV A1		



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



CAP FOR HEADER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN01MAR2018  
BASVESH WARAD

CHK01MAR2018  
GUERRIERO, SHAYNIA

APVD01MAR2018  
GUERRIERO, SHAYNIA

DIMENSIONS:  
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -  
1 PLC ± -  
2 PLC ± -  
3 PLC ± .015  
4 PLC ± -  
ANGLES ± 1°

MATERIAL-

FINISH-

PRODUCT SPEC-

APPLICATION SPEC-

WEIGHT-

01MAR2018  
A2

00779

C=2331450

TE Connectivity

NAME  
MTA100 HDR ASSY,SM,FL,SN, HT, T&R

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
C=2331450

RESTRICTED TO  
-

CUSTOMER DRAWING

SCALE  
10:1

SHEET  
3 OF 3

REV  
A1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2331450-4](#)