






ALL CONTACTS



52.10	51.40	50	5-2373375-0
50.10	49.40	48	4-2373375-8
48.10	47.40	46	4-2373375-6
46.10	45.40	44	4-2373375-4
44.10	43.40	42	4-2373375-2
42.10	41.40	40	4-2373375-0
40.10	39.40	38	3-2373375-8
38.10	37.40	36	3-2373375-6
36.10	35.40	34	3-2373375-4
34.10	33.40	32	3-2373375-2
32.10	31.40	30	3-2373375-0
30.10	29.40	28	2-2373375-8
28.10	27.40	26	2-2373375-6
26.10	25.40	24	2-2373375-4
24.10	23.40	22	2-2373375-2
22.10	21.40	20	2-2373375-0
20.10	19.40	18	1-2373375-8
18.10	17.40	16	1-2373375-6
16.10	15.40	14	1-2373375-4
14.10	13.40	12	1-2373375-2
12.10	11.40	10	1-2373375-0
10.10	9.40	8	2373375-8
8.10	7.40	6	2373375-6
DIM "F"	DIM "E"	POS.	TE PN.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANKIT YADAV CHK KARTHIK J. APVD PRASHANTH S.	11NOV2019 25NOV2019 27NOV2019
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±2°	PRODUCT SPEC 108-64040 APPLICATION SPEC 114-32259
MATERIAL SEE NOTES		FINISH SEE NOTES	
-		WEIGHT -	
		CUSTOMER DRAWING	

		TE Connectivity			
		NAME AMPMODU 2mm SHROUDED HEADER DUAL ROW, VERTICAL SMD, SN, TUBE			
SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO
A2	00779	C=2373375			-
		SCALE	5:1	SHEET	1 OF 1
					REV A

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2373375-0](#)