



SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC



PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)



SEZIONE A:A



SEZIONE C:C




NOTE:

- 1 ADATTO PER TERMINALE MASCHIO CON FORO, SECONDO FIGURA Z
- 2 MASSIMA SCIABOLATURA AMMESSA: 8 mm PER METRO

3 SPAZIO MIN. OCCUPATO DAL BLOCCHETTO
PN. 281734-1 0 -2

4 ONLY WELDED SPLICES
ALLOWED

FIGURA Z



STAGNATO	OTTONE OT 70	281737-2
FINITURA / COLORE (FINISH / COLOUR)	MATERIALE (MATERIAL)	NUMERO (PART NUMBER)
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION 19
© COPYRIGHT 1985 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING		
TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO	DIAH. ISOLANTE (INS. DIA. RANGED)	RANGO FILO (WIRE RANGED)
TOLERANCES, UNLESS OTHERWISE SPECIFIED	2.2-3.4 mm	0.5-2.3 mm ²
± 0.3	TE Connectivity	
± 2°	DESCRIZIONE (DESCRIPTION) .312 SERIES POSITIVE LOCK REC. FLAG TYPE R	
ANGOLI (ANGLES)	LOC. SIZE	NUMERO (CNS. NO.)
DIS. V. RANIERI (DR.) 20-1-86	I A3 C-281737-F	
CONT. (CNS.)	REV. H1	FOLIO (SHEET) DI (OF)
APP. (APP.)		

REV.	REVISIONI (REVISION RECORD)	DIS. DATA (DR. DATE)
H1	REVISED PER ECR-20-012400	SS 25 SEP 80
H	REVISED A.B. (8700-0275-97) C.T. A.B. 09/81	
E	AGGIORNATO 16 JUNE 88	
D	AGGIORNATO 6/11/88	
C	AGG. NOTA 3	AB 8-10-88
B	AGGIORNATO	AB 10-2-88
A	AGGIORNATO	2/86
SIMILE AL PN. 172796		

DISTRIBUZIONE
PRINT. DIST.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[281737-2](#)