

D

C

B

A

D

C



B

A




© 2019 TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	09DEC2019	AY	PS
	A1	DIMENSION F REMOVED FROM PCB LAYOUT	11JUN2020	AY	PS



- NOTES:
- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
CONTACT PIN : COPPER ALLOY
FINISH :
MATING SIDE: MIN. 0.1 µm GOLD OVER NICKEL UNDER PLATING.
SOLDER SIDE: MIN. 2.0 µm TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TUBE (WITH PICK AND PLACE CAP)
- △ TOLERANCE NOT CUMULATIVE.



2-2842244-0 AS SHOWN

44	50.85	52.65	50	5-2842244-0
38	44.85	46.65	44	4-2842244-4
34	40.85	42.65	40	4-2842244-0
28	34.85	36.65	34	3-2842244-4
24	30.85	32.65	30	3-2842244-0
20	26.85	28.65	26	2-2842244-6
18	24.85	26.65	24	2-2842244-4
14	20.85	22.65	20	2-2842244-0
10	16.85	18.65	16	1-2842244-6
8	14.85	16.65	14	1-2842244-4
DIM "G"	DIM "F"	DIM "E"	POS.	TE PN.

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12NOV2019 ANKIT YADAV
DIMENSIONS: mm		CHK 25NOV2019 KARTHIK JK
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 27NOV2019 PRASHANTH S.
0 PLC ± 1 PLC ± 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±° FINISH		PRODUCT SPEC 108-64040
MATERIAL SEE NOTES -		APPLICATION SPEC 114-32259
		WEIGHT -
		CUSTOMER DRAWING

TE Connectivity			
NAME AMPMODU 2mm, SHROUDED HEADER, DUAL ROW, VERTICAL SMD, 0.1 Au, TUBE WITH PICK AND PLACE CAP			
SIZE A2	CAGE CODE 100779	DRAWING NO C=2842244	RESTRICTED TO -
SCALE 5:1		SHEET 1 OF 1	REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2842244-0](#)