

D

C

B

A



D

C



B

A


© 2019 TE Connectivity. All Rights Reserved.



- NOTES:
- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH : MIN. 2.0 µm TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TUBE (WITH PICK AND PLACE CAP)
- △3 TOLERANCE NOT CUMULATIVE.



2-2842273-0 AS SHOWN



RECOMMENDED PCB PATTERN

52.10	51.40	50	5-2842273-0
50.10	49.40	48	4-2842273-8
48.10	47.40	46	4-2842273-6
46.10	45.40	44	4-2842273-4
44.10	43.40	42	4-2842273-2
42.10	41.40	40	4-2842273-0
40.10	39.40	38	3-2842273-8
38.10	37.40	36	3-2842273-6
36.10	35.40	34	3-2842273-4
34.10	33.40	32	3-2842273-2
32.10	31.40	30	3-2842273-0
30.10	29.40	28	2-2842273-8
28.10	27.40	26	2-2842273-6
26.10	25.40	24	2-2842273-4
24.10	23.40	22	2-2842273-2
22.10	21.40	20	2-2842273-0
20.10	19.40	18	1-2842273-8
18.10	17.40	16	1-2842273-6
16.10	15.40	14	1-2842273-4
14.10	13.40	12	1-2842273-2
12.10	11.40	10	1-2842273-0
DIM "F"	DIM "E"	POS.	TE PN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ±
	2 PLC ±0.25
	3 PLC ±
	4 PLC ±
MATERIAL SEE NOTES	FINISH SEE NOTES
-	

DWN ANKIT YADAV 11NOV2019			
CHK KARTHIK JK 25NOV2019			
APVD PRASHANTH S. 27NOV2019	NAME AMPMODU 2mm SHROUDED HEADER DUAL ROW, VERTICAL SMD, SN, TUBE, WITH PICK AND PLACE CAP		
PRODUCT SPEC 108-64040	SIZE A2	CAGE CODE 00779	DRAWING NO C-2842273
APPLICATION SPEC 114-32259	RESTRICTED TO -	SCALE 5:1	SHEET 1 OF 1
WEIGHT -	REV A1		
CUSTOMER DRAWING			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-2842273-2](#)