



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	28NOV2019	AY	PS
	A1	REMOVE POSITION 4, 6 AND 8	04 JUN2020	AY	PS



 TOLERANCE NOT CUMULATIVE.

ALL CONTACTS

52.10	51.40	50	5-2842276-0
50.10	49.40	48	4-2842276-8
48.10	47.40	46	4-2842276-6
46.10	45.40	44	4-2842276-4
44.10	43.40	42	4-2842276-2
42.10	41.40	40	4-2842276-0
40.10	39.40	38	3-2842276-8
38.10	37.40	36	3-2842276-6
36.10	35.40	34	3-2842276-4
34.10	33.40	32	3-2842276-2
32.10	31.40	30	3-2842276-0
30.10	29.40	28	2-2842276-8
28.10	27.40	26	2-2842276-6
26.10	25.40	24	2-2842276-4
24.10	23.40	22	2-2842276-2
22.10	21.40	20	2-2842276-0
20.10	19.40	18	1-2842276-8
18.10	17.40	16	1-2842276-6
16.10	15.40	14	1-2842276-4
14.10	13.40	12	1-2842276-2
12.10	11.40	10	1-2842276-0
DIM "F"	DIM "E"	POS.	TE PN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANKIT YADAV	11NOV2019
DIMENSIONS:		CHK KARTHIK J.	25NOV2019
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD PRASHANTH S.	27NOV2019
	0 PLC	±	PRODUCT SPEC 108-64040 APPLICATION SPEC 114-32259
	1 PLC	±	
	2 PLC	±0.25	
	3 PLC	±	
	4 PLC	±	
MATERIAL	ANGLES	±2°	
SEE NOTES	FINISH	SEE NOTES	WEIGHT
-	-	-	CUSTOMER DRAWING

		TE Connectivity	
NAME AMPMODU 2mm SHROUDED HEADER DUAL ROW, VERTICAL SMD, 0.76 Au,TUBE, WITH PICK AND PLACE CAP			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	Ⓒ=2842276	-
		SCALE 5:1	SHEET 1 OF 1
			REV A1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2842276-2](#)