

D

C

B

A



D

C



B

A


© 2019 TE Connectivity. All Rights Reserved.



- NOTES:
- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH : MIN. 2.0 µm TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TAPE AND REEL (WITH PICK AND PLACE CAP)
- 3 TOLERANCE NOT CUMULATIVE.



2-2842277-0 AS SHOWN



RECOMMENDED PCB PATTERN

52.10	51.40	50	5-2842277-0
50.10	49.40	48	4-2842277-8
48.10	47.40	46	4-2842277-6
46.10	45.40	44	4-2842277-4
44.10	43.40	42	4-2842277-2
42.10	41.40	40	4-2842277-0
40.10	39.40	38	3-2842277-8
38.10	37.40	36	3-2842277-6
36.10	35.40	34	3-2842277-4
34.10	33.40	32	3-2842277-2
32.10	31.40	30	3-2842277-0
30.10	29.40	28	2-2842277-8
28.10	27.40	26	2-2842277-6
26.10	25.40	24	2-2842277-4
24.10	23.40	22	2-2842277-2
22.10	21.40	20	2-2842277-0
20.10	19.40	18	1-2842277-8
18.10	17.40	16	1-2842277-6
16.10	15.40	14	1-2842277-4
14.10	13.40	12	1-2842277-2
12.10	11.40	10	1-2842277-0
DIM "F"	DIM "E"	POS.	TE PN.

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ±
	2 PLC ±0.25
	3 PLC ±
	4 PLC ±
MATERIAL	FINISH
SEE NOTES	SEE NOTES
-	-

DWN 11NOV2019 CHK 25NOV2019 APVD 27NOV2019	ANKIT YADAV KARTHIK JK PRASHANTH S.	TE Connectivity
PRODUCT SPEC	108-64040	NAME AMPMODU 2mm SHROUDED HEADER DUAL ROW, VERTICAL SMD, SN, T/R, WITH PICK AND PLACE CAP
APPLICATION SPEC	114-32259	SIZE A2
WEIGHT -	CAGE CODE 00779	DRAWING NO C=2842277
CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1
		REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2842277-0](#)