

D

C

B

A

D

C

B





A

© 2019 TE Connectivity. All Rights Reserved.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	09DEC2019	AY	PS
	A1	REMOVE POSITION 4, 6 AND 8	04JUN2020	AY	PS


- NOTES:
- MATERIAL
HOUSING & P&P CAP : HIGH TEMPERATURE THERMOPLASTIC, UL94-V0; COLOR- BLACK
POST : COPPER ALLOY
FINISH : MIN. 2.0 µm TIN OVER NICKEL UNDER PLATING.
 - PACKAGING: TAPE AND REEL (WITH PICK AND PLACE CAP)
- △ 3 TOLERANCE NOT CUMULATIVE.



52.10	51.40	50	5-2842289-0
50.10	49.40	48	4-2842289-8
48.10	47.40	46	4-2842289-6
46.10	45.40	44	4-2842289-4
44.10	43.40	42	4-2842289-2
42.10	41.40	40	4-2842289-0
40.10	39.40	38	3-2842289-8
38.10	37.40	36	3-2842289-6
36.10	35.40	34	3-2842289-4
34.10	33.40	32	3-2842289-2
32.10	31.40	30	3-2842289-0
30.10	29.40	28	2-2842289-8
28.10	27.40	26	2-2842289-6
26.10	25.40	24	2-2842289-4
24.10	23.40	22	2-2842289-2
22.10	21.40	20	2-2842289-0
20.10	19.40	18	1-2842289-8
18.10	17.40	16	1-2842289-6
16.10	15.40	14	1-2842289-4
14.10	13.40	12	1-2842289-2
12.10	11.40	10	1-2842289-0
DIM "F"	DIM "E"	POS.	TE PN.



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE WAVE



RECOMMENDED PCB HOLE PATTERN FOR THROUGH HOLE REFLOW /PIN-IN-PASTE

2-2842289-0 AS SHOWN

PICK AND PLACE CAP	3
CONTACT PIN	2
HOUSING	1
DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ANKIT YADAV 11NOV2019
		CHK KARTHIK JK 25NOV2019
		APVD PRASHANTH S. 27NOV2019
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC
	0 PLC ±	108-64040
	1 PLC ±	APPLICATION SPEC
	2 PLC ±0.25	114-32259
	3 PLC ±	WEIGHT -
	4 PLC ±	CUSTOMER DRAWING
	ANGLES ±°	SCALE 5:1
MATERIAL SEE NOTES	FINISH SEE NOTES	SHEET 1 OF 1
		REV A1

		TE Connectivity	
NAME		AMPMODU 2mm SHROUDED HEADER DUAL ROW, VERTICAL TH, SN, T/R, WITH PICK AND PLACE CAP	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	©=2842289	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2842289-2](#)