





THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION - , - .
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
ES	00	P	LTR	DESCRIPTION	DATE	APVD
			-	SEE SHEET 1	-	-

TYPE 2	61.5	57.5	6.2	52.4	30.5	56	37.1	±0.15 26.2	700	20	BLACK	7-292228-0
	61.5	57.5	6.2	52.4	29.0	56	35.6		700	19		6-292228-9
	49.5	45.5	6.2	40.4	27.5	44	34.1	20.2±0.15	700	18		6-292228-8
	49.5	45.5	6.2	40.4	26.0	44	32.6		700	17		6-292228-7
	49.5	45.5	6.2	40.4	24.5	44	31.1		700	16		6-292228-6
	49.5	45.5	6.2	40.4	23.0	44	29.6		700	15		6-292228-5
	49.5	45.5	6.2	40.4	21.5	44	28.1		700	14		6-292228-4
	49.5	45.5	6.2	40.4	20.0	44	26.6		700	13		6-292228-3
	49.5	45.5	6.2	40.4	18.5	44	25.1		700	12		6-292228-2
	49.5	45.5	6.2	40.4	17.0	44	23.6		700	11		6-292228-1
	37.5	33.5	6.2	28.4	15.5	32	22.1	14.2	700	10		6-292228-0
	37.5	33.5	6.2	28.4	14.0	32	20.6	14.2	700	9		5-292228-9
	37.5	33.5	6.2	28.4	12.5	32	19.1	14.2	700	8		5-292228-8
	37.5	33.5	6.2	28.4	11.0	32	17.6	14.2	700	7		5-292228-7
TYPE 1	29.5	25.5	6.2	-	9.5	24	16.1	11.5	700	6		5-292228-6
	29.5	25.5	6.2	-	8.0	24	14.6	11.5	700	5		5-292228-5
	29.5	25.5	6.2	-	6.5	24	13.1	11.5	700	4		5-292228-4
	29.5	25.5	4.7	-	5.0	24	11.6	11.5	700	3		5-292228-3
	29.5	25.5	2.8	-	3.5	24	10.1	11.5	700	2		5-292228-2
TAPE TYPE	W2	W1	F	E	D	C	B	A	QTY/ REEL	POS	COLOR	ON TAPE P/N
DIMENSIONS												

OBSOLETED	TYPE 2	61.5	57.5	6.2	52.4	30.5	56	37.1	±0.15 26.2	700	20	BEIGE	2-292228-0	
		61.5	57.5	6.2	52.4	29.0	56	35.6		700	19		1-292228-9	
		49.5	45.5	6.2	40.4	27.5	44	34.1	20.2±0.15	700	18		1-292228-8	
		49.5	45.5	6.2	40.4	26.0	44	32.6		700	17		1-292228-7	
		49.5	45.5	6.2	40.4	24.5	44	31.1		700	16		1-292228-6	
		49.5	45.5	6.2	40.4	23.0	44	29.6		700	15		1-292228-5	
		49.5	45.5	6.2	40.4	21.5	44	28.1		700	14		1-292228-4	
		49.5	45.5	6.2	40.4	20.0	44	26.6		700	13		1-292228-3	
		49.5	45.5	6.2	40.4	18.5	44	25.1		700	12		1-292228-2	
		49.5	45.5	6.2	40.4	17.0	44	23.6		700	11		1-292228-1	
		37.5	33.5	6.2	28.4	15.5	32	22.1	14.2	700	10		1-292228-0	
		37.5	33.5	6.2	28.4	14.0	32	20.6	14.2	700	9		292228-9	
		37.5	33.5	6.2	28.4	12.5	32	19.1	14.2	700	8		292228-8	
		37.5	33.5	6.2	28.4	11.0	32	17.6	14.2	700	7		292228-7	
		TYPE 1	29.5	25.5	6.2	-	9.5	24	16.1	11.5	700		6	292228-6
			29.5	25.5	6.2	-	8.0	24	14.6	11.5	700		5	292228-5
			29.5	25.5	6.2	-	6.5	24	13.1	11.5	700		4	292228-4
			29.5	25.5	4.7	-	5.0	24	11.6	11.5	700		3	292228-3
			29.5	25.5	2.8	-	3.5	24	10.1	11.5	700		2	292228-2
	TAPE TYPE	W2	W1	F	E	D	C	B	A	QTY/ REEL	POS	COLOR	ON TAPE P/N	
		DIMENSIONS												

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S.XU 31JAN03		 TE Connectivity											
				CHK S.YAO 31JAN03													
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD T.SASAKI 31JAN03		NAME											
				PRODUCT SPEC		AMP Mini CT Connector 1.5mm PITCH											
				108-60018		SINGLE ROW POST HDR ASS'Y (H)											
				APPLICATION SPEC		SMT TYPE WITHOUT BOSS, EMBOSS TAPE PACKAGED											
MATERIAL				FINISH		114-5223		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
				WEIGHT		A3		00779		C-292228		—					
CUSTOMER DRAWING						SCALE		NTS		SHEET		2 OF 4		REV		C3	

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION
- . - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC
ES

DIST
00


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1.078	36.5	34.5	30.6	28.5	20	7-292228-0	2-292228-0
1.033	35.0	33.0	29.1	27.0	19	6-292228-9	1-292228-9
0.988	33.5	31.5	27.6	25.5	18	6-292228-8	1-292228-8
0.942	32.0	30.0	26.1	24.0	17	6-292228-7	1-292228-7
0.896	30.5	28.5	24.6	22.5	16	6-292228-6	1-292228-6
0.850	29.0	27.0	23.1	21.0	15	6-292228-5	1-292228-5
0.804	27.5	25.5	21.6	19.5	14	6-292228-4	1-292228-4
0.759	26.0	24.0	20.1	18.0	13	6-292228-3	1-292228-3
0.713	24.5	22.5	18.6	16.5	12	6-292228-2	1-292228-2
0.667	23.0	21.0	17.1	15.0	11	6-292228-1	1-292228-1
0.621	21.5	19.5	15.6	13.5	10	6-292228-0	1-292228-0
0.576	20.0	18.0	14.1	12.0	9	5-292228-9	292228-9
0.530	18.5	16.5	12.6	10.5	8	5-292228-8	292228-8
0.484	17.0	15.0	11.1	9.0	7	5-292228-7	292228-7
0.438	15.5	13.5	9.6	7.5	6	5-292228-6	292228-6
0.392	14.0	12.0	8.1	6.0	5	5-292228-5	292228-5
0.347	12.5	10.5	6.6	4.5	4	5-292228-4	292228-4
0.301	11.0	9.0	5.1	3.0	3	5-292228-3	292228-3
0.255	9.5	7.5	3.6	1.5	2	5-292228-2	292228-2
WEIGHT (g)	E	C	B	A	Pos.	BLACK	BEIGE (NAT)
	DIMENSIONS					P/N	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH -

MATERIAL

-

DWN
S.XU
31JAN03

CHK
S.YAO
31JAN03

APVD
T.SASAKI
31JAN03

PRODUCT SPEC
108-60018

APPLICATION SPEC
114-5223

WEIGHT
-

CUSTOMER DRAWING

 TE Connectivity

NAME
AMP Mini CT Connector 1.5mm PITCH
SINGLE ROW POST HDR ASS'Y (H)
SMT TYPE WITHOUT BOSS, EMBOSS TAPE PACKAGED

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-292228

RESTRICTED TO
-

SCALE
NTS

SHEET
4 OF 4

REV
C3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-292228-6](#)