


THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY ALL RIGHTS RESERVED

LOC	DIST	REVISIONS			
		P	LIR	DESCRIPTION	DATE
FB	00		A2	REVISED PER	ECR-16-012124
					07DEC16
					T.Q
					W.H



TYPE 1







TYPE 2

TOLERANCES UNLESS OTHERWISE SPECIFIED:


10> : ±0.2  
30> \* >10 : ±0.25  
100> \* >30 : ±0.3  
ANGLE : ±3°

NOTE:  
1. PEELING STRENGTH: 0.20-0.69N (20-70gf)  
PEELING ANGLE: 165-180°  
PEELING SPEED: 300mm/MINUTE.



		DWN S. XU 31JAN03	 <b>TE Connectivity</b>	
		CHK S. YAO 31JAN03		
DIMENSIONS:  mm		APVD T. SASAKI 31JAN03	NAME  AMP Mini Common Terminated (CT) Connector 1.5mm PITCH SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS, POLYIMIDE TAPE, EMBOSS TAPE PACKAGED	
		PRODUCT SPEC  108-60018		
		APPLICATION SPEC  114-5223	SIZE A3	
		WEIGHT	CAGE CODE 00779	
MATERIAL		CUSTOMER DRAWING	DRAWING NO C-292232	
TOLERANCES UNLESS OTHERWISE SPECIFIED:			RESTRICTED TO	
0 PLC ±			-	
1 PLC ±				
2 PLC ±				
3 PLC ±				
4 PLC ±				
ANGLES ±				
FINISH				

LOC	DIST	REVISIONS				DATE	DWN	APVD
FB	00	P	LTR	DESCRIPTION				
				SEE SHEET 1				



TYPE 2	49.5	45.5	5.0	9.5	40.4	29.9	44	32.9	20.2±0.15	500	20	BEIGE	2-292232-0
	49.5	45.5	5.0	9.5	40.4	28.4	44	31.4		500	19		1-292232-9
	49.5	45.5	5.0	9.5	40.4	26.9	44	29.9		500	18		1-292232-8
	49.5	45.5	5.0	9.5	40.4	25.4	44	28.4		500	17		1-292232-7
	49.5	45.5	5.0	9.5	40.4	23.9	44	26.9		500	16		1-292232-6
	49.5	45.5	5.0	9.5	40.4	22.4	44	25.4		500	15		1-292232-5
	49.5	45.5	5.0	9.5	40.4	20.9	44	23.9		500	14		1-292232-4
	49.5	45.5	5.0	9.5	40.4	19.4	44	22.4		500	13		1-292232-3
	37.5	33.5	5.0	9.5	28.4	17.9	32	20.9	14.2	500	12		1-292232-2
	37.5	33.5	5.0	9.5	28.4	16.4	32	19.4	14.2	500	11		1-292232-1
	37.5	33.5	5.0	9.5	28.4	14.9	32	17.9	14.2	500	10		1-292232-0
	37.5	33.5	5.0	6.5	28.4	13.4	32	16.4	14.2	500	9		292232-9
TYPE 1	29.5	25.5	5.0	6.5	-	11.9	24	14.9	11.5	500	8		292232-8
	29.5	25.5	5.0	6.5	-	10.4	24	13.4	11.5	500	7		292232-7
	29.5	25.5	5.0	6.5	-	8.9	24	11.9	11.5	500	6		292232-6
	29.5	25.5	5.0	9.5	-	7.4	24	10.4	11.5	500	5		292232-5
	21.5	17.5	5.0	8.0	-	5.9	16	8.9	7.5	500	4		292232-4
	21.5	17.5	5.0	6.5	-	4.4	16	7.4	7.5	500	3		292232-3
TAPE TYPE	W2	W1	G	F	E	D	C	B	A	QTY/REEL	POS	COLOR	ON TAPE P/N

DIMENSIONS

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC  
1 PLC  
2 PLC  
3 PLC  
4 PLC  
ANGLES

±



DWN

CHK

APVD

PRODUCT SPEC

SEE SHEET 1

APPLICATION SPEC

SEE SHEET 1

WEIGHT

CUSTOMER DRAWING

MATERIAL

FINISH



TE Connectivity

NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH

SINGLE ROW POST HDR ASS'Y (V) SMT TYPE

WITH POLYIMIDE TAPE, WITH BOSS, EMBOSS TAPE PACKAGED

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A4 00779 G-292232

SCALE

NON

SHEET

2

OF

4

REV

A2

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

© COPYRIGHT — BY — ALL RIGHTS RESERVED.

LOC
FB

151

## REVISIONS

P	LIR
---	-----









DESCRIPTION
-------------

TABLE

— 124 —

APVU



SEE SHEET 1



SHOWN AS WIHTOUT TAPE

NOTES:

NOTES:  
1. MATERIAL:  
HOUSING: GLASS FILLED, HIGH HEAT RESISTANT NYLON, UL94V-0, COLOR: BEIGE OR BLACK  
POST: Sn-100% BRASS WIRE  
△ TO BE MEASURED WITH CONNECTOR PLACED ON HORIZONTAL DATUM SURFACE,  
FLOAT OF SOLDER TIME FROM DATUM SURFACE IS 0.1mm MAX.

		DWN		 TE Connectivity							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK		NAME					
mm				APVD		AMP MINI COMMON TERMINATION (CT) CONNECTOR 1.5 mm PITCH					
		0 PLC ±		PRODUCT SPEC		SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS					
		1 PLC ±									
		2 PLC +		APPLICATION SPEC		SIZE					
		3 PLC ±				CAGE CODE		DRAWING NO		RESTRICTED TO	
		4 PLC ±				A3		00779		C-292232	
MATERIAL		FINISH		WEIGHT							
SEE NOTE 1		SEE NOTE 1		CUSTOMER DRAWING		SCALE		NON		SHEET 3 OF 4	
										REV A2	

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

BY -  
COPYRIGHT -

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1	-	-	-

0.98	31.5	32.5	30.6	28.5	20	2-292232-0
0.93	30.0	31.0	29.1	27.0	19	1-292232-9
0.89	28.5	29.5	27.6	25.5	18	1-292232-8
0.84	27.0	28.0	26.1	24.0	17	1-292232-7
0.80	25.5	26.5	24.6	22.5	16	1-292232-6
0.75	24.0	25.0	23.1	21.0	15	1-292232-5
0.71	22.5	23.5	21.6	19.5	14	1-292232-4
0.66	21.0	22.0	20.1	18.0	13	1-292232-3
0.62	19.5	20.5	18.6	16.5	12	1-292232-2
0.57	18.0	19.0	17.1	15.0	11	1-292232-1
0.52	16.5	17.5	15.6	13.5	10	1-292232-0
0.48	15.0	16.0	14.1	12.0	9	292232-9
0.43	13.5	14.5	12.6	10.5	8	292232-8
0.39	12.0	13.0	11.1	9.0	7	292232-7
0.34	10.5	11.5	9.6	7.5	6	292232-6
0.30	9.0	10.0	8.1	6.0	5	292232-5
0.25	7.5	8.5	6.6	4.5	4	292232-4
0.20	6.0	7.0	5.1	3.0	3	292232-3
WEIGHT (g)	D	C	B	A	Pos.	BEIGE (NAT)
	DIMENSIONS					P/N

DIMENSIONS: mm	DWN	MATERIAL SEE SHEET 1	FINISH SEE SHEET 1
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	 <b>TE Connectivity</b>	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APVD		
	PRODUCT SPEC	NAME AMP MINI COMMON TERMINATED (CT) CONNECTOR 1.5 mm PITCH SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS	
	APPLICATION SPEC	SIZE A4	CAGE CODE 00779
	WEIGHT	DRAWING NO G=292232	RESTRICTED TO
CUSTOMER DRAWING		SCALE NON	SHEET 4 OF 4
		REV A2	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[292232-7](#)