

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

BY

ALL RIGHTS RESERVED

LOC

DIST

REVISIONS

P

LIR

DESCRIPTION

DATE

OWN

APVD

A2


REVISED PER

ECR-16-012124


07DEC16

T.Q

W.H



TYPE 1



TYPE 2

TOLERANCES UNLESS OTHERWISE SPECIFIED:

10> : ±0.2
30> * >10 : ±0.25
100> * >30 : ±0.3
ANGLE : ±3°


NOTE:

1. PEELING STRENGTH: 0.20-0.69N (20-70gf)

PEELING ANGLE: 165-180°

PEELING SPEED: 300mm/MINUTE.



ADHESIVE TAPE





FLANGE

SECURE TO FLANGE WITH ADHESIVE TAPE


COVER TAPE



OFF TOP OF REEL

		DWN S.XU	31JAN03	 TE Connectivity				
		CHK S.YAO	31JAN03					
		APVD T.SASAKI	31JAN03	NAME				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		AMP Mini Common Terminated (CT) Connector 1.5mm PITCH				
		<div>0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±</div>		SINGLE ROW POST HDR ASS'Y (V) SMT TYPE				
MATERIAL		FINISH		SIZE A3		CAGE CODE 00779	DRAWING NO C-292232	RESTRICTED TO
								-
CUSTOMER DRAWING				SCALE NON		SHEET 1		OF 4
								REV A2

LOC	DIST	REVISIONS				DATE	DWN	APVD
FB	00	P	LTR	DESCRIPTION				
SEE SHEET 1								




TYPE 2	49.5	45.5	5.0	9.5	40.4	29.9	44	32.9	20.2±0.15	500	20	BEIGE	2-292232-0
	49.5	45.5	5.0	9.5	40.4	28.4	44	31.4		500	19		1-292232-9
	49.5	45.5	5.0	9.5	40.4	26.9	44	29.9		500	18		1-292232-8
	49.5	45.5	5.0	9.5	40.4	25.4	44	28.4		500	17		1-292232-7
	49.5	45.5	5.0	9.5	40.4	23.9	44	26.9		500	16		1-292232-6
	49.5	45.5	5.0	9.5	40.4	22.4	44	25.4		500	15		1-292232-5
	49.5	45.5	5.0	9.5	40.4	20.9	44	23.9		500	14		1-292232-4
	49.5	45.5	5.0	9.5	40.4	19.4	44	22.4		500	13		1-292232-3
	37.5	33.5	5.0	9.5	28.4	17.9	32	20.9	14.2	500	12		1-292232-2
	37.5	33.5	5.0	9.5	28.4	16.4	32	19.4	14.2	500	11		1-292232-1
37.5	33.5	5.0	9.5	28.4	14.9	32	17.9	14.2	500	10	1-292232-0		
37.5	33.5	5.0	6.5	28.4	13.4	32	16.4	14.2	500	9	292232-9		
TYPE 1	29.5	25.5	5.0	6.5	-	11.9	24	14.9	11.5	500	8	292232-8	
	29.5	25.5	5.0	6.5	-	10.4	24	13.4	11.5	500	7	292232-7	
	29.5	25.5	5.0	6.5	-	8.9	24	11.9	11.5	500	6	292232-6	
	29.5	25.5	5.0	9.5	-	7.4	24	10.4	11.5	500	5	292232-5	
	21.5	17.5	5.0	8.0	-	5.9	16	8.9	7.5	500	4	292232-4	
	21.5	17.5	5.0	6.5	-	4.4	16	7.4	7.5	500	3	292232-3	
TAPE TYPE	W2	W1	G	F	E	D	C	B	A	QTY/REEL	POS	COLOR	ON TAPE P/N
DIMENSIONS													

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES



DWN
CHK
APVD
PRODUCT SPEC
SEE SHEET 1
APPLICATION SPEC
SEE SHEET 1
WEIGHT

MATERIAL	FINISH
TE Connectivity	
NAME AMP Mini Common Terminated (CT) Connector 1.5mm PITCH	
SINGLE ROW POST HDR ASS'Y (V) SMT TYPE	
WITH POLYIMIDE TAPE, WITH BOSS, EMOSS TAPE PACKAGED	
SIZE	CAGE CODE
A4	00779
DRAWING NO	RESTRICTED TO
G-292232	-

CUSTOMER DRAWING

SCALE

NON

SHEET

2

OF

4

REV

A2

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

© COPYRIGHT — BY — ALL RIGHTS RESERVED.








LOC
FB

151

REVISIONS



SEE SHEET 1000

DATE	OWN	APVD
------	-----	------



NOTES:

1. MATERIAL:
HOUSING: GLASS FILLED, HIGH HEAT RESISTANT NYLON, UL94V-0, COLOR: BEIGE OR BLACK
POST: Sn-100% BRASS WIRE
△ TO BE MEASURED WITH CONNECTOR PLACED ON HORIZONTAL DATUM SURFACE,
FLOAT OF SOLDER TIME FROM DATUM SURFACE IS 0.1mm MAX.

			DWN		 TE Connectivity												
			CHK														
DIMENSIONS:			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME												
mm					AMP MINI COMMON TERMINATION (CT) CONNECTOR 1.5 mm PITCH												
			0 PLC ±		SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS												
			1 PLC ±														
			2 PLC +														
			3 PLC ±														
			4 PLC ±														
			ANGLES ± ±														
MATERIAL			FINISH		APPLICATION SPEC		SIZE			CAGE CODE	DRAWING NO	RESTRICTED TO					
SEE NOTE 1			SEE NOTE 1		WEIGHT		A3		00779	C-292232							
CUSTOMER DRAWING										SCALE	NON	SHEET	3	OF	4	REV	A2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

BY

© COPYRIGHT

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
				SEE SHEET 1	-	-	-

0.98	31.5	32.5	30.6	28.5	20	2-292232-0
0.93	30.0	31.0	29.1	27.0	19	1-292232-9
0.89	28.5	29.5	27.6	25.5	18	1-292232-8
0.84	27.0	28.0	26.1	24.0	17	1-292232-7
0.80	25.5	26.5	24.6	22.5	16	1-292232-6
0.75	24.0	25.0	23.1	21.0	15	1-292232-5
0.71	22.5	23.5	21.6	19.5	14	1-292232-4
0.66	21.0	22.0	20.1	18.0	13	1-292232-3
0.62	19.5	20.5	18.6	16.5	12	1-292232-2
0.57	18.0	19.0	17.1	15.0	11	1-292232-1
0.52	16.5	17.5	15.6	13.5	10	1-292232-0
0.48	15.0	16.0	14.1	12.0	9	292232-9
0.43	13.5	14.5	12.6	10.5	8	292232-8
0.39	12.0	13.0	11.1	9.0	7	292232-7
0.34	10.5	11.5	9.6	7.5	6	292232-6
0.30	9.0	10.0	8.1	6.0	5	292232-5
0.25	7.5	8.5	6.6	4.5	4	292232-4
0.20	6.0	7.0	5.1	3.0	3	292232-3
WEIGHT (g)	D	C	B	A	Pos.	BEIGE (NAT)
	DIMENSIONS					P/N

DIMENSIONS: mm	DWN	MATERIAL SEE SHEET 1	FINISH SEE SHEET 1
TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK	 TE Connectivity	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	APVD		
	PRODUCT SPEC	NAME AMP MINI COMMON TERMINATED (CT) CONNECTOR 1.5 mm PITCH SINGLE ROW POST HDR ASS'Y (V) SMT TYPE WITH BOSS	
	APPLICATION SPEC	SIZE A4	CAGE CODE 00779
	WEIGHT	DRAWING NO G-292232	RESTRICTED TO
CUSTOMER DRAWING		SCALE NON	SHEET 4 OF 4
		REV A2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[292232-4](#)