






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
1	-		-	SEE SHEET 1	-	-

POLARIZATION TYPES

TYPE "A"




TYPE "B"




P/Ns: 0-293606-1,
1-293606-1

P/Ns: 0-293606-2,
1-293606-2

TYPE "C"



TYPE "D"



P/Ns: 0-293606-3,
1-293606-3

P/Ns: ~~0-293606-4,~~
~~1-293606-4,~~

TABLE 1						
OBSOLETE		D	BLACK	SOCKET HOUSING PANEL MOUNT VERS. NECTOR* M-LINE	A	1-293606-4
		C	BLACK	SOCKET HOUSING PANEL MOUNT VERS. NECTOR* M-LINE	C	1-293606-3
		B	BLACK	SOCKET HOUSING PANEL MOUNT VERS. NECTOR* M-LINE	C	1-293606-2
		A	BLACK	SOCKET HOUSING PANEL MOUNT VERS. NECTOR* M-LINE	C	1-293606-1
OBSOLETE		D	NATURAL	SOCKET HOUSING PANEL MOUNT VERS. NECTOR* M-LINE	A	0-293606-4
		C	NATURAL	SOCKET HOUSING PANEL MOUNT VERS. NECTOR* M-LINE	C	0-293606-3
		B	NATURAL	SOCKET HOUSING PANEL MOUNT VERS. NECTOR* M-LINE	C	0-293606-2
		A	NATURAL	SOCKET HOUSING PANEL MOUNT VERS. NECTOR* M-LINE	C	0-293606-1
MATERIAL		POL. KEYING	COLOUR	DESCRIPTION	REV.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

SEE NOTES

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±°

1 PLC ±0.3

2 PLC ±0.20

3 PLC ±°

4 PLC ±°

ANGLES ±3°

FINISH -

DWN
M. ZUCCA
06SEP2010

CHK
M. ZUCCA
06SEP2010

APVD
G. TURCO
06SEP2010

PRODUCT SPEC
108-20304

APPLICATION SPEC
114-20152

WEIGHT
~5.9 g

Customer Drawing

TE Connectivity

NAME
SOCKET HOUSING
PANEL MOUNT VERSION
NECTOR* M-LINE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-293606

RESTRICTED TO
-

SCALE
2:1




SHEET
2


OF
4

REV
C1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
1	-	-	-	SEE SHEET 1	-	-

PANEL / WALL
SUGGESTED CUT OUT




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. ZUCCA 06SEP2010	 TE Connectivity		
DIMENSIONS: mm		CHK M. ZUCCA 06SEP2010			
		APVD G. TURCO 06SEP2010	NAME SOCKET HOUSING PANEL MOUNT VERSION NECTOR* M-LINE		
		PRODUCT SPEC 108-20304	SIZE A300779		
MATERIAL SEE NOTES		APPLICATION SPEC 114-20152	CAGE CODE C-293606		
		WEIGHT ~5.9 g	DRAWING NO Customer Drawing		
TOLERANCES UNLESS OTHERWISE SPECIFIED:			RESTRICTED TO -		
		0 PLC ± 1 PLC ±0.3 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ±3° FINISH -	SCALE 2:1		
			SHEET 3 OF 4		
			REV C1		

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
1	-		-	SEE SHEET 1	-	-


PANEL / WALL
SUGGESTED CUT OUT FOR
MULTIPLE HOLES ON MULTIPLE ROWS


(PITCH CAN BE ADJUSTED TO CUSTOMER
NEED BUT IN ANY CASE MUST NOT BE LESS
THAN 30.00 mm)



PANEL / WALL
SUGGESTED CUT OUT FOR
MULTIPLE HOLES ON SINGLE ROW

(PITCH CAN BE ADJUSTED TO CUSTOMER
NEED BUT IN ANY CASE MUST NOT BE LESS
THAN 30.00 mm)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. ZUCCA	06SEP2010	 TE Connectivity		
		CHK M. ZUCCA	06SEP2010			
		APVD G. TURCO	06SEP2010	NAME SOCKET HOUSING PANEL MOUNT VERSION NECTOR* M-LINE		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-20304		RESTRICTED TO
		0 PLC ±° 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±° 4 PLC ±° ANGLES ±3°		APPLICATION SPEC 114-20152		
MATERIAL SEE NOTES		FINISH -		WEIGHT ~5.9 g		-
				Customer Drawing		
				SCALE 2:1	SHEET 4 OF 4	REV C1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[293606-1](#)