

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

NOTES:

1 MATERIAL: POLYAMIDE GLASS FILLED
COLOUR NATURAL

2 MATERIAL: POLYAMIDE GLASS FILLED
COLOUR BLACK

3) PACKAGING: SEE TE PACKAGING
SPECIFICATION 107-20294

4 TE LOGO

5 N CODE

6 L CODE

7 PE CODE

8 RATED VOLTAGE

9 WIRE SIZE & RATED CURRENT






10 AREA FOR AGENCY APPROVAL LOGO

11 IP CODE


12) SOCKET CAP P/N 293596-1 (SEE DRAWING 293596
FOR REFERENCE) HAS TO BE ASSEMBLED TO GUARANTEE
IP40 DEGREE OF PROTECTION WHEN CONNECTOR HOUSING IS NOT MATTED WITH
COUNTERPART.

13 DATE CODE

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
-	-	D1		PARTS -2 -3 1-2 AND 1-3 RELEASED FOR PRODUCTION	27JUN2013	JC
		E		UPDATED DRAWING	19DEC2014	MZ
		E1		REVISED PART NUMBERS	17JUL2017	MZ
		E2		REVISED PER ECR-18-006945	20SEP2018	MZ



SCALE 1:1



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm			
		0 PLC	±0.3
		1 PLC	±0.20
		2 PLC	±0.20
		3 PLC	±0.20
		4 PLC	±0.20
		ANGLES	±3°
MATERIAL		FINISH	-

DWN	M. ZUCCA	06OCT2009
CHK	U. AIME	06OCT2009
APVD	G. TURCO	06OCT2009
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	



TE Connectivity

NAME
T-SPLITTER CONNECTOR
ECTOR* M-LINE
3 POLES UNSEALED VERSION

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-293611	-

Customer Drawing









SCALE 2:1

SHEET 1 OF 2

REV E2

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
-	-		-	SEE SHEET 1	-	-


POLARIZATION TYPES

TYPE "A"	TYPE "B"
 	 
P/Ns: 293611-1, 1-293611-1	P/Ns: 293611-2, 1-293611-2
TYPE "C"	TYPE "D"
 	 
P/Ns: 293611-3, 1-293611-3	P/Ns: 293611-4, 1-293611-4

OBSOLETE		UNSEALED	B	BLACK	T-SPLITTER CONNECTOR NECTOR* M-LINE	C	1-293611-4
		UNSEALED	C	BLACK	T-SPLITTER CONNECTOR NECTOR* M-LINE	E	1-293611-3
		UNSEALED	B	BLACK	T-SPLITTER CONNECTOR NECTOR* M-LINE	E	1-293611-2
		UNSEALED	A	BLACK	T-SPLITTER CONNECTOR NECTOR* M-LINE	E	1-293611-1
OBSOLETE		UNSEALED	B	NATURAL	T-SPLITTER CONNECTOR NECTOR* M-LINE	C	293611-4
		UNSEALED	C	NATURAL	T-SPLITTER CONNECTOR NECTOR* M-LINE	E	293611-3
		UNSEALED	B	NATURAL	T-SPLITTER CONNECTOR NECTOR* M-LINE	E	293611-2
		UNSEALED	A	NATURAL	T-SPLITTER CONNECTOR NECTOR* M-LINE	E	293611-1
NOTE		VERSION	POL. KEYING	COLOUR	DESCRIPTION	REV.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES

±
±0.3
±0.20
±
±
±3°

MATERIAL

-

FINISH

-

DWN
M. ZUCCA
CHK
U. AIME
APVD
G. TURCO

06OCT2009
06OCT2009
06OCT2009

PRODUCT SPEC
-
APPLICATION SPEC
-
WEIGHT
-

NAME
T-SPLITTER CONNECTOR
NECTOR* M-LINE
3 POLES UNSEALED VERSION

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-293611

RESTRICTED TO
-

Customer Drawing

SCALE
1:1

SHEET
2

OF
2

REV
E2

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-293611-1](#)