




D



C


B

A



LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
	A2	REVISED			18MAR2013	DC	JC	
	A3	RELEASED 293660-3, -5, -6			30SEP2013	DC	JC	
	A4	RELEASED 1-293660-1, -2, -3, -5, -6			28FEB2014	KR	JC	
	A5	RELEASED 293660-4, 1-4			05MAR2014	KR	JC	

- 1 MATERIAL: PA GF (NATURAL AND BLACK COLOUR)
- 2 NUMBER OF CABLE CORES (n) AND CONDUCTORS SIZE (s.s)
- 3 AREA FOR TE LOGO
- 4 AREA FOR TE P/N



1	11.30	10.45±0.75	H05VV5-F	5GX1.5	BLACK	1-293660-6	A
1	15.60	14.75±0.75	H05VV5-F	7GX2.5	BLACK	1-293660-5	A
1	7.90	7.60±0.10	RZI-LSF-OH	-	BLACK	1-293660-4	A
1	13.50	12.65±0.75	H05VV5-F	5GX2.5 7GX1.5	BLACK	1-293660-3	A
1	11.40	11.10±0.10	RZI-LSF-OH	6GX2.5	BLACK	1-293660-2	A
1	10.00	9.70±0.10	RZI-LSF-OH	6GX1.5	BLACK	1-293660-1	A
1	11.30	10.45±0.75	H05VV5-F	5GX1.5	NATURAL	293660-6	A
1	15.60	14.75±0.75	H05VV5-F	7GX2.5	NATURAL	293660-5	A
1	7.90	7.60±0.10	RZI-LSF-OH	-	NATURAL	293660-4	A
1	13.50	12.65±0.75	H05VV5-F	5GX2.5 7GX1.5	NATURAL	293660-3	A
1	11.40	11.10±0.10	RZI-LSF-OH	6GX2.5	NATURAL	293660-2	A
1	10.00	9.70±0.10	RZI-LSF-OH	6GX1.5	NATURAL	293660-1	A
NOTE	DIM "D" NOM.	CABLE OUTSIDE Ø	CABLE TYPE	CONDUCTOR NR. & SIZE (sqmm)	COLOUR	PART NO.	REV.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
A. BERNARD
21 JAN 2011

CHK
U. AIME
21 JAN 2011

APVD
G. TURCO
21 JAN 2011

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±0.3

2 PLC ±0.2

3 PLC ±-

4 PLC ±-

ANGLES ±3°

FINISH

MATERIAL

SEE NOTES

PRODUCT SPEC
108-20324

APPLICATION SPEC
114-20169

WEIGHT
-

Customer Drawing

TE Connectivity

NAME
RING NUT FOR CABLE RETENTION (5,6,7 POLES) NECTOR M-LINE UNSEALED VERSION

SIZE
A2

CAGE CODE
b0779

DRAWING NO
C-293660

RESTRICTED TO
-

SCALE
4:1

SHEET
1

OF
1

REV
A5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-293660-3](#)