






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
	-		7	REVISED MARKINGS	17SEP2013	KR	JC
			A	PARTS RELEASED FOR PRODUCTION	13NOV2013	KR	JC
			C	ECR-15-011011	27JUL2015	RS	PO
			CI	REVISED PER ECR-18-006945	30MAY2018	NG	MZ



NOTES:

- 1 MATERIAL: PA GF (NATURAL AND BLACK COLOUR)
- 2 ALL POLARIZATION KEYS SHOWN FOR REF ONLY
- 3 WAYS I.D.
- 4 CURRENT RATING
- 5 VOLTAGE RATING
- 6 RIB CLOSING CAVITIES BY CHANGE OVER
- 7 TE LOGO
- 8 TE PART NUMBER
- 9 DATA CODE AND CAVITY I.D.
- 10 AREA FOR AGENCIES APPROVAL LOGO
- 11) SEE C-DRAWING 293682 (LOCKING CAP) TO GET IP 40
- 12 IP CODE
- 13 SLOTS TO ALLOW DELATCHING TOOL OPERATION. FOR DEALTCHING TOOL AND DOPERATION REFER TO APPLICATION SPECIFICATION



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. BERNARDI CHK M. ZUCCA APVD G. TURCO	31MAR2011 31MAR2011 31MAR2011	TE Connectivity		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SKT HOUSING 6 POLES PANEL MOUNT NECTOR M-LINE UNSEALED VERSION		
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		± ±0.3 ±0.20 ± ± ±3°		SIZE A260779		
MATERIAL		NOTE 1		DRAWING NO C-293673		
				RESTRICTED TO -		
				SCALE 3:1		
				SHEET 1 OF 3		
				REV CI		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
	-		-	SEE SHEET 1	-	-	-







POLARIZATION TYPES		
POLARIZATION TYPE "C"	POLARIZATION TYPE "B"	POLARIZATION TYPE "C"
		
PNs 0-293673-3 AND 1-293673-3	PNs 0-293673-4 AND 1-293673-4	PNs 0-293673-5 AND 1-293673-5

TABLE 1					
OBSOLETE		E	BLACK	SOCKET HSG 6 POLES PANEL MOUNT NECTOR* M-LINE	A 1-293673-5
		D	BLACK	SOCKET HSG 6 POLES PANEL MOUNT NECTOR* M-LINE	A 1-293673-4
OBSOLETE		C	BLACK	SOCKET HSG 6 POLES PANEL MOUNT NECTOR* M-LINE	A 1-293673-3
		E	NATURAL	SOCKET HSG 6 POLES PANEL MOUNT NECTOR* M-LINE	A 0-293673-5
OBSOLETE		D	NATURAL	SOCKET HSG 6 POLES PANEL MOUNT NECTOR* M-LINE	A 0-293673-4
		C	NATURAL	SOCKET HSG 6 POLES PANEL MOUNT NECTOR* M-LINE	A 0-293673-3
NOTE	POL. KEYING	COLOUR	DESCRIPTION	REV.	P/N


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. BERNARD1 31MAR2011	 TE Connectivity			
DIMENSIONS: mm		CHK M. ZUCCA 31MAR2011				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.3 2 PLC ±0.20 3 PLC ± 4 PLC ± ANGLES ±3° FINISH	APVD G. TURCO 31MAR2011	NAME SKT HOUSING 6 POLES PANEL MOUNT NECTOR M-LINE UNSEALED VERSION			
		PRODUCT SPEC 108-20324				
MATERIAL	NOTE 1	APPLICATION SPEC 114-20169	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		WEIGHT -	A200779		C-293673	-
Customer Drawing			SCALE	3:1	SHEET 2 OF 3	REV C1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
	-		-	SEE SHEET 1	-	-


PN 293673-3 AS SHOWN



PANEL/WALL
SUGGESTED LAYOUT



3D VIEWS,
FOR REFERENCE ONLY
PN 293673-3 AS SHOWN



SCALE 1:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. BERNARDI CHK M. ZUCCA APVD G. TURCO	31MAR2011 31MAR2011 31MAR2011	TE Connectivity	
DIMENSIONS: mm		PRODUCT SPEC 108-20324		NAME SKT HOUSING 6 POLES PANEL MOUNT NECTOR M-LINE UNSEALED VERSION	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±3° FINISH		APPLICATION SPEC 114-20169		SIZE A2	CAGE CODE 0779
MATERIAL		WEIGHT -		DRAWING NO C-293673	RESTRICTED TO -
NOTE 1		Customer Drawing		SCALE 3:1	SHEET 3 OF 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-293673-1](#)