







LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	26SEP2012	-	JE
			A1	EOL BY ECR-19-019907	02JAN2020	A.L	H.L




- CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
- 0.76µm MIN MATTE TIN OVER 1.27µm MIN NICKEL
- MATERIAL:
CONTACT - COPPER ALLOY
SHIELD - PHOSPHER BRONZE
HOUSING AND CHICKLET - GLASS FILLED POLYESTER
- REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS
- DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER
- SEATING HEIGHT TO BOARD SURFACE
- CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- DATE CODE
- PART NUMBER



RECOMMENDED PRINTED
CIRCUIT BOARD LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD
SCALE 4:1

OBsolete



THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN S.J. MAGARO 14SEP2004		5120949-1	
				CHK R.A. PATTERSON 14SEP2004		PART NUMBER	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -		NAME	
mm		0 PLC ±.1		PRODUCT SPEC		RECEPTACLE ASSEMBLY, 6 ROW, 60 POSITION, VERTICAL, W/GUIDE MODULE, Z-PACK HS3	
		1 PLC ±.1		108-1957			
		2 PLC ±0.13		APPLICATION SPEC			
		3 PLC ±0.050					
		4 PLC ±.1		114-13020		SIZE	
MATERIAL		FINISH		WEIGHT		CAGE CODE DRAWING NO	
		SHIELD: 1		-		A100779C=5120949	
		CONTACTS: 2		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE		SHEET 1 OF 1	
						REV A1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5120949-1](#)