


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 09/04/92 J. LOCONDRÒ		 TE Connectivity	
		CHK. 01/26/93 S. HEADER			
DIMENSIONS: mm		TO REVISIONS UNLESS OTHERWISE SPECIFIED:		APPROV. 1/26/93 D. BACCHETTI	
		0 PLC ± —		NAME RECEPTACLE ASSEMBLY, SIGNAL MODULE, Z-PACK 2mm FB, 4 ROW, 3.5mm LEAD LENGTH	
		1 PLC ± —			
		2 PLC ± .13			
		3 PLC ± —			
MATERIAL		ANGLES ± —		SIZE CAGE CODE DRAWING NO.	
		FINISH		RESTRICTED TO	
				—	
		WEIGHT 0.000000		A1 00779 C 536510	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV. AD	



- ① HOUSING MATERIAL: LIQUID CRYSTAL POLYMER.
COLOR: NATURAL.
- ② CONTACT MATERIAL: PHOSPHOR-BRONZE.
- ③ CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT) —
0.00127 MIN. NICKEL
ON MATING SURFACES—
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT
ON LEADS—
0.00381 MIN. TIN-LEAD, OVER UNDERPLATE
LUBRICATION (ENTIRE CONTACT):
SURFACE CONDITIONER PER TYCO SPEC 112-1002 AFTER PLATING.
- ④ PART MARKING PER AMP INCORPORATED SPECIFICATION 115-9009, LOCATED
APPROXIMATELY AS SHOWN.
- ⑤ CUSTOMIZED PART, HOUSING MOLDED WITHOUT END GUIDE LUGS.
- ⑥ OBSOLETE PART NUMBER.
- ⑦ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-536510-3](#)