






REVISIONS					
F	T	LTR	DESCRIPTION	DATE	DWN APVD
F			REVISED PER ECO-20-013368	28SEP2020	RZ HL

D



C

B

A



- △ HOUSING MATERIAL: LIQUID CRYSTAL POLYMER PER ASTM D5138 LCP000 G30A 32250, COLOR: NATURAL.
- △ CONTACT MATERIAL: PHOSPHOR-BRONZE.
- △ CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT) —
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290.
ON MATING SURFACES—
CONFORMS TO ALL TESTING SPECIFIED FOR TELCORDIA
UNCONTROLLED ENVIRONMENT
ON LEADS—
0.0006 MIN TIN PER ASTM B 545, OVER UNDERPLATE
LUBRICATION (MIN MATING SURFACES)
SURFACE CONDITIONER AFTER PLATING.
- △ PART MARKING, LOCATED APPROXIMATELY AS SHOWN.
- △ CONTACT FINISH:
UNDERPLATE (ENTIRE CONTACT) —
0.00127 MIN NICKEL PER SAE-AMS-QQ-N-290.
ON MATING SURFACES—
0.00076 MIN NICKEL OR COBALT HARDENED GOLD
PER ASTM B-488 OVER UNDERPLATE.
ON LEADS—
0.0006 MIN TIN PER ASTM B 545, OVER UNDERPLATE
LUBRICATION (MIN MATING SURFACES)
SURFACE CONDITIONER AFTER PLATING.
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- △ TE OR TE CONNECTIVITY LOGO IS LOCATED.



RECOMMENDED CIRCUIT PATTERN
PER IPC-D300 TYPE II, CLASS C
(COMPONENT SIDE)

OBSOLETE	NO	46	23	47.88	△	96	3-5536511-3
	NO	22	11	23.88	△	48	3-5536511-2
OBSOLETE	YES	10	5	11.88	△	24	3-5536511-1
	NO	34	17	35.88	△	72	1-5536511-2
OBSOLETE	NO	130	65	131.88	△	264	1-5536511-1
	NO	106	53	107.88	△	216	1-5536511-0
△	NO	118	59	119.88	△	240	5536511-9
	NO	82	41	83.88	△	168	5536511-8
OBSOLETE	NO	66	33	67.88	△	136	5536511-7
	NO	58	29	59.88	△	120	5536511-6
OBSOLETE	NO	70	35	71.88	△	144	5536511-5
	NO	94	47	95.88	△	192	5536511-4
	NO	46	23	47.88	△	96	5536511-3
	NO	22	11	23.88	△	48	5536511-2
	YES	10	5	11.88	△	24	5536511-1
POSITIONING PEGS	C	B	A	FINISH	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER	31AUG04	 TE Connectivity	
		CHK R. WERTZ	31AUG04		
DIMENSIONS: mm		APVD R. WERTZ	31AUG04	NAME RCPT. ASSY, SIGNAL MODULE, Z-PACK 2mm FB 4 ROW, 3.55mm PRESS FIT LEAD LENGTH	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
				APPLICATION SPEC	
				SIZE	
				CAGE CODE	
MATERIAL		WEIGHT		DRAWING NO	
		0.000000		A1 00779	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE	
				4:1	
				SHEET	
				1 OF 1	
				REV	
				F	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5536511-3](#)