



D7CF

REV.
B

REVISIONS			RELEASED	
REV.	DESCRIPTION	DATE	APPROVED	
A	14-006972 RELEASE TO PRODUCTION	14-05-09	DAW	
B	14-017267 10-32 TORQUE WAS 19.8 TO 24.2	14-11-14	DAW	
C	15-005578 ADD ITEN 10, HS LABEL	15-04-10	ACH	



INSTALLATION TORQUE
 6-32 = 5.4 TO 6.6 IN-LBS
 10-32 = 18.0 TO 20.0 IN-LBS



CONSTRUCTION	GASKET SEALED
CONFIGURATION	3PDT
CONTACT RATING	245 A, 28 VDC CARRY ONLY INTERMITTENT DUTY 30 SEC PER THROW, THEN 5 MIN OFF
COIL RATING	28 VDC / 126 OHMS ± 10%
MIN OPER AMBIENT TEMP	-55° C
MAX OPER AMBIENT TEMP	+85° C
ELECTRICAL LIFE	30,000 CYCLES
WEIGHT	14 OZ MAX

10	1	55820SOCN	HS LABEL			3-1616995-6	
9	9	51810-054	LOCKWASHER, #10 SPLIT			9-1616360-2	BRONZE
8	2	51806-014	WASHER LOCK #6 SPLIT			1616360-7	BRONZE
7	9	51712-194	WASHER 7/16 .203-ID .031-TK			2-1616359-6	
6	2	51702-204	WASHER 3/8 X 9/64 X .032			1-1616358-9	
5	9	50410-084	NUT 10-32 X 3/8 X 1/8 HEX			1616339-7	
4	2	50406-034	NUT 6-32 X 1/4 X 3/32 HEX			5-1616337-3	BRASS
3	1	48251-001	PLATE - WIRING DIAGRAM			1-1616978-6	
2	1	28497-130	PRIMARY ASSEMBLY			5-1616982-5	
1	1	16043-001	PLATE - NAME			3-1616169-5	
FIND NO	QTY REQD	PART OR IDENTIFYING NO	NOMENCLATURE OR DESCRIPTION	DRAWING OR SPECIFICATION	FSCM NO	TE PART NO	MATERIAL OR NOTE

UNLESS OTHERWISE SPECIFIED
 DIMENSIONS ARE IN INCHES
 TOLERANCES ON

2 PL DEC. 3 PL DEC. 1 ANGLES
 ±.06 ±.010 ± 1°

CONFIGURATION CONTROLLED
 HAMILTON SUNDSTRAND
 EP 4953087

DR BY DAW 12-08-17
 CHK BY MDM 14-05-09
 ENGR DAW 12-08-17
 MFG DWA 14-05-09

SIZE A CODE IDENT 74063

SCALE 1:1 SHEET 1 OF 1

STE
 Hartman Division 175 N. DIAMOND STREET MANSFIELD, OHIO 44902

3PDT STARTER CONTACTOR

DWG NO. D7CF

REF TE PN 5-1616982-4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1616982-4](#)