


LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			A	REVISED PER ECR-08-007741	08JUL08	HMR
						APVD
						GJ

D


C

B


A




- 1 CONTINUOUS STRIP ON REELS
- 2 VERTICAL BURRS NOT TO EXCEED 0.13 [.005] ALONG THIS EDGE
- 3 PRE-PLATED TIN.



SECTION A-A



SECTION B-B



F OR O	8.89 [.350]	6.35 [.250]	F	4.57 [.180]	3.45 [.136]	2 3.0mm ² 2 [12]
					3.23 [127]	5.0mm ² [10]
					2.87 [113]	3.0mm ² [12]
					2.64 [104]	2.0mm ² [14]
					2.52 [099]	1.3mm ² [16]
TYPE	WIDTH	STRIP LENGTH ±0.38 [±.015]	TYPE	WIDTH	HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

3	7.87 OR 2 (4.32) DIA 5.59 [.310] OR 2 [.170] DIA [.220]	1.3-5.5mm ² OR 2 (3.0mm ²) [16-10] OR 2 [12] AWG	63496-2
	FINISH	INSULATION RANGE	WIRE RANGE
THIS DRAWING IS A CONTROLLED DOCUMENT.		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		POWER RING	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		SIZE CAGE CODE DRAWING NO	
MATERIAL		RESTRICTED TO	
082 BRASS		A2 00779 C=63496	
SEE TABLE		CUSTOMER DRAWING	
		SCALE 4:1	SHEET 1 OF 1
		REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[63496-1](#)