




1. PART NUMBER CHANGES AND/OR DESIGN CHANGES AFFECTING ITEM INTERCHANGEABILITY REQUIRE PRIOR TYCO APPROVAL AND AUTHORIZATION BY REVISION TO THIS DRAWING.
2. ITEMS PROVIDED TO THIS SPECIFICATION SHALL BE IDENTIFIED ON THE CONTAINER WITH THE FOLLOWING INFORMATION:
PART NUMBER & DATE CODE OF MANUFACTURE.
- 3 MATERIAL: PIN CONTACT: COPPER ALLOY
CONICAL WASHER: SPRING STEEL
SCREW & FLAT WASH.: STEEL
- 4 FINISH: PIN CONTACT: SILVER PLATE .00020 MIN THICK
OVER NICKEL .000040 MIN THICK.
SCREW: ZINC PLATE
CONICAL & FLAT WASH.: NICKEL PLATE
- 5 RECOMMENDED HOLE DIAMETER AFTER PLATING:
ØDIM.D±.002.

CI	6648224-3	0.057	0.064	0.250	0.244	0.731	0.281
CI	6648224-2	0.057	0.064	0.250	0.244	0.550	0.100
	6648224-1	0.112	0.118	0.267	0.261	0.550	0.100
	PART NUMBER	DIM. A	DIM. B	DIM. C	DIM. D	DIM. E	DIM. F

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G.PETERS 01MAY2007		TE Connectivity	
DIMENSIONS: INCHES		CHK D.ORRIS 01MAY2007			
		APVD S.FLICKINGER 01MAY2007			
		PRODUCT SPEC -			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -		NAME PIN CONTACT, SIZ4 #4, SCREW MOUNT, LOCKING STYLE, PRESS FIT	
0 PLC ±-		WEIGHT -		SIZE A3	
1 PLC ±-		CUSTOMER DRAWING		CAGE CODE 00779	
2 PLC ±.02[.5]		SCALE 2:1		DRAWING NO C-6648224	
3 PLC ±.010[.25]		SHEET 1 OF 1		REV CI	
4 PLC ±-					
ANGLES ±.5					
MATERIAL -					
FINISH -					
material_2					
finish_spec_2					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6648224-2](#)