





THIS DRAWING IS A CONTROLLED DOCUMENT.										DWG. C. RICHARD 3-19-90		 TE Connectivity	
DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009										CHK. W. G. LENKER 3-22-90			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D. J. ASSINI PRODUCT SPEC		NAME		SOCKET CONTACT, SIZE 20 DF, 20-24 AWG, AMPLIMITE					
		0 PLC ± —		1 PLC ± —		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		1 PLC ± 0.13 [0.005]		APPLICATION SPEC		A1		00779		C-66504		—	
		3 PLC ± —											
		4 PLC ± —											
		4 ANGLES ± —											
FINISH		 SEE TABLE		WEIGHT —		CUSTOMER DRAWING		SCALE 15:1		SHEET 1 of 1		REV. APR	
MATERIAL PHOSPHOR BRONZE PER QQ-B-750													

SECTION B-B
SCALE 20:1
WIRE BARREL

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66504-8](#)