




SWITCH SPECIFICATION		
SWITCH ACTION		SPDT
MAX. SWITCHING VOLTAGE	(VDC)	100
	(VRMS)	70
MAX. SWITCHING CURRENT	(AMPS)	0.5
DC CONTACT RATING	(WATTS)	3
MIN. BREAKDOWN VOLTAGE	(VDC)	200
INITIAL CONTACT RESISTANCE	(OHMS)	0.25

						UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETRES TOLERANCES ARE :- DECIMALS ANGLES		CAD GENERATED DRAWING DO NOT MANUALLY DUPLICATE		GENTECH INTERNATIONAL LIMITED GIRVAN, AYRSHIRE,U.K.				
REVISION	A	B	C				DRAWN		WJG 10.06.98		PART NAME LS804-31			
CHANGE ORDER No	—	5359	6190				CHECKED		CL 26.06.98					
DATE	—	21.05.01 MW	16.11.04 MW				APPROVED		RMM 29.06.98					
APPROVED	—	WJG 24.05.01	IH 16.11.04								SIZE A3	ARTICLE No 80507-000	REV C	
THIS DRAWING IS THE PROPERTY OF GENTECH International Limited AND SHOULD NOT BE COPIED OR USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY				MATERIAL			LNP POLYPROPYLENE GRADE MFX 1006HS			DO NOT SCALE DRAWING				
				FINISH						SCALE			3:2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[80507-000](#)