


PARTS LIST			
ITEM NO.	ARTICLE NO.	DESCRIPTION	QTY REQD

2-WAY PACKARD CONNECTOR
PER WACKER DRAWING 79979
WITH PACKARD TERMINALS
(Part No. 12010771)




CABLE: 2 CONDUCTORS #22 AWG (26/36 TIN SOFT
COPPER WITH PVC INSULATION)
BLACK GLOSS POLYURETHANE JACKET Ø4.3 nom.

Float: NBR Rubber

GROMMET: NITRILE, 55 SHORE HARDNESS ± 5

CIRCLIP: STAINLESS STEEL


SWITCH: COTO RI46



FILTER UNIT MOUNTING HOLE DIMENSIONS:
 $\varnothing 19.40 \pm 0.1$ by 4.80 ± 0.1 thickness

FITTING INSTRUCTIONS

- 1) SENSOR IS SUPPLIED WITH GROMMET LOOSE FROM FITTING.
(SEE SKETCH BELOW)
- 2) PUSH GROMMET INTO MOUNTING HOLE ON FILTER UNIT.
- 3) APPLY LUBRICANT TO PUSH-FIT FEATURE OF SENSOR.
- 4) PRESS SENSOR HOME INTO GROMMET.



REFERENCE DRAWINGS: WACKER PART / DRAWING NUMBER 160663
GTI DEVELOPMENT DRG P0901-07 revB

REVISION	A					
CHANGE ORDER NO.	-					
DATE	-					
APPROVED	-					

THIS DRAWING IS THE PROPERTY OF GENTECH International Limited
AND SHOULD NOT BE COPIED OR USED FOR MANUFACTURE OR OTHERWISE
DISCLOSED WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY. ©

MATERIAL SEE NOTES

FINISH **BLACK**

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETRES
TOLERANCES ARE :
MARKED ON DIMENSIONS

CAD
GENERATED DRAWING
DO NOT
MANUALLY DUPLICATE

DRAWN	FM 02/04/04
CHECKED	KJM 02/04/04
APPROVED	IH 02/04/04

DO NOT SCALE DRAWING

GENTECH INTERNATIONAL LIMITED
GIRVAN, Ayrshire, U.K.

PART NAME

VS-X0901C
OIL LEVEL SENSOR

SIZE
A3

ARTICLE NO.
81539-000

REV.
A

SCALE 1:2

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[81539-000](#)