


| REVISIONS | | | | | |
|-----------|-----|---------------------------|-----------|-----|------|
| P | LTR | DESCRIPTION | DATE | DWN | APVD |
| | B | REVISED PER ECR-20-013258 | 21SEP2020 | GK | MN |

LABEL AND LINER DESIGN




All dimensions in mm [Inches]

TE PN: E42900-000


**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 2500**


PRESENTATION



| | |
|---------------|-------------------------------------|
| MATERIAL | HIGH TACK MATTE METALIZED POLYESTER |
| ADHESIVE TYPE | PERMANENT ACRYLIC |
| LINER | GLASSINE PAPER |

| TOLERANCES mm [INCH] | |
|----------------------|--------------|
| LABEL HEIGHT: | ±0.3 [.012] |
| LABEL WIDTH: | ±0.3 [.012] |
| WEB WIDTH: | ±0.8 [.031] |
| VERTICAL REPEAT: | ±0.8 [.031]* |
| HORIZONTAL REPEAT: | ±0.8 [.031]* |
| PRINT POSITIONING: | ±0.8 [.031]* |
| LEFT MARGIN : | ±0.4 [.016] |
| QUANTITY : | -0 % +2 % |
| *NON ACCUMULATING | |

| | |
|---|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | |
| DIMENSIONS: mm [INCHES] | TOLERANCES UNLESS OTHERWISE SPECIFIED. |
|  | <div style="display: flex; justify-content: space-between;"> <div> 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES </div> <div> $\pm -$ $\pm -$ $\pm -$ $\pm -$ $\pm -$ $\pm -$ </div> </div> |
| MATERIAL | FINISH |
| SEE TABLE | - |

| | | | | | | | |
|------------------|-----------|---|-----|-------|--------|-----|---|
| DWN | 150CT2020 |  TE Connectivity | | | | | |
| GOPALAKRISHNA HV | | | | | | | |
| CHK | 150CT2020 | NAME HMM – HIGH TACK MATTE METALIZED POLYESTER LABELS — — | | | | | |
| MIKE NUTTALL | | | | | | | |
| APVD | 150CT2020 | | | | | | |
| MIKE NUTTALL | | | | | | | |
| PRODUCT SPEC | | SIZE CAGE CODE DRAWING NO RESTRICTED TO | | | | | |
| TTDS—118 | | | | | | | |
| APPLICATION SPEC | | | | | | | |
| — | | A3C2290C—HMM—762508—2.5—8A | | | | | |
| WEIGHT 0.504g | | — | | | | | |
| CUSTOMER DRAWING | | SCALE | NTS | SHEET | 1 OF 1 | REV | B |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[E42900-000](#)