

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT 2020 TE Connectivity Ltd.

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	INITIAL CUSTOMER DRAWING	20JAN2020	AFK	LS


FLATTENED WIDTH




D

d


w




EXPANDED TUBING PRODUCT



SPOOL



SPOOL I.D.  
101 (4.0)




Product Size	2.4	3.2	4.8	6.4	9.5	12	18	25	38
"D" Minimum Supplied I.D.	2.4 (.094)	3.2 (.126)	4.8 (.189)	6.4 (.252)	9.5 (.374)	12.7 (.500)	19.1 (.752)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	0.8 (.031)	1.1 (.043)	1.6 (.063)	2.1 (.083)	3.2 (.126)	4.2 (.165)	6.4 (.252)	8.5 (.335)	19.1 (.752)
"w" Recovered Wall Thickness ±0.08 (.003)	0.51 (.020)	0.51 (.020)	0.58 (.023)	0.58 (.023)	0.61 (.024)	0.61 (.024)	0.61 (.024)	0.64 (.025)	0.64 (.025)
Minimum Sleeve Flattened Width	4.30 (.169)	5.82 (.229)	8.00 (.315)	10.65 (.419)	15.5 (.610)	20.4 (.803)	30.5 (1.201)	40.4 (1.591)	60.3 (2.374)

NOTES:  
1. ALL DIMENSIONS ARE IN MILLIMETERS (inches).

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL  
CROSSLINKED POLYOLEFIN

DWN AFK 09JAN2020

CHK -


APVD LS 20JAN2020

PRODUCT SPEC  
RW-2519

APPLICATION SPEC  
-

WEIGHT VARIOUS

CUSTOMER DRAWING

 TE Connectivity

NAME  
D-CT  
OUTSIDE PRINTER SPOOL  
-

SIZE  
A3

CAGE CODE  
0198G

DRAWING NO  
C-MCD170014

RESTRICTED TO  
-

SCALE  
-

SHEET  
1 OF 1

REV  
2

1470-19 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EL8083-000](#)