


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	INITIAL RELEASE	06JUL2020	MN	AK

LABEL AND LINER DESIGN




All dimensions in mm [Inches]

TE PN: F67510-000

**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 1300**


PRESENTATION




MATERIAL	METALIZED POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

<p>DIMENSIONS:</p> <p>mm [INCHES]</p>	<p>TOLERANCES UNLESS OTHERWISE SPECIFIED:</p>												
	<table border="0"> <tr> <td>0 PLC</td><td>± —</td></tr> <tr> <td>1 PLC</td><td>± —</td></tr> <tr> <td>2 PLC</td><td>± —</td></tr> <tr> <td>3 PLC</td><td>± —</td></tr> <tr> <td>4 PLC</td><td>± —</td></tr> <tr> <td>ANGLES</td><td>± —</td></tr> </table>	0 PLC	± —	1 PLC	± —	2 PLC	± —	3 PLC	± —	4 PLC	± —	ANGLES	± —
0 PLC	± —												
1 PLC	± —												
2 PLC	± —												
3 PLC	± —												
4 PLC	± —												
ANGLES	± —												
<p>MATERIAL</p> <p>SEE TABLE</p>	<p>FINISH</p> <p>—</p>												

DWN	06JUL2020	<div>TE Connectivity</div>						
M.NUTTALL								
CHK	06JUL2020	NAME MP – METALIZED POLYESTER LABELS — —						
M.NUTTALL								
APVD	06JUL2020							
A. KEAN								
PRODUCT SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO						
TTDS-074								
APPLICATION SPEC								
—		A3C2290G=MP-101101-1.3-8A—						
WEIGHT0.929g								
CUSTOMER DRAWING			SCALE	NTS	SHEET	1 OF 1	REV	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[F67510-000](#)