



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	INITIAL RELEASE	06JUL2020	MN	AK

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: E21509-000

OUTSIDE WOUND


LABEL ACROSS: 4

PER ROLL QTY: 25000


MATERIAL	METALIZED POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

<p>DIMENSIONS: mm [INCHES]</p>	<p>TOLERANCES UNLESS OTHERWISE SPECIFIED:</p>												
	<table border="0"> <tr> <td>0 PLC</td><td>± .1</td></tr> <tr> <td>1 PLC</td><td>± .05</td></tr> <tr> <td>2 PLC</td><td>± .03</td></tr> <tr> <td>3 PLC</td><td>± .02</td></tr> <tr> <td>4 PLC</td><td>± .01</td></tr> <tr> <td>ANGLES</td><td>± .5</td></tr> </table>	0 PLC	± .1	1 PLC	± .05	2 PLC	± .03	3 PLC	± .02	4 PLC	± .01	ANGLES	± .5
0 PLC	± .1												
1 PLC	± .05												
2 PLC	± .03												
3 PLC	± .02												
4 PLC	± .01												
ANGLES	± .5												
<p>MATERIAL</p>	<p>FINISH</p>												
<p>SEE TABLE</p>	<p>—</p>												

DWN	06JUL2020
M. NUTTALL	
CHK	06JUL2020
M. NUTTALL	
APVD	06JUL2020
A. KEAN	
PRODUCT SPEC	
TTDS-074	
APPLICATION SPEC	
—	
WEIGHT	0.008 g
CUSTOMER DRAWING	

		TE Connectivity	
		NAME	
MP – METALIZED POLYESTER LABELS			
—			
—			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	Ⓒ=MP-165051-25-8A	—
SCALE		SHEET	REV
NTS		1 OF 1	C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[E21509-000](#)