



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL RELEASE	06JUL2020	MN	AK

LABEL AND LINER DESIGN



PRESENTATION




All dimensions in mm [Inches]

TE PN: F14201-000

**OUTSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 2500**

MATERIAL	METALIZED POLYESTER
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:
		 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —
MATERIAL SEE TABLE		FINISH —

DWN	06JUL2021
M. NUTTALL	
CHK	06JUL2021
M. NUTTALL	
APVD	06JUL2021
A. KEAN	
PRODUCT SPEC	
TTDS-074	
APPLICATION SPEC	
—	
WEIGHT	0.230g
CUSTOMER DRAWING	

0		 TE Connectivity	
0			
0		NAME	
		MP – METALIZED POLYESTER LABELS	
		—	
		—	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	C=MP-610419-2.5-8A	—
		SCALE	SHEET
		N.T.S.	1 OF 1
		REV	B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[F14201-000](#)