THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	24NOV2016	DW	CW







PANEL CUT OUT DIMENSION FOR INSERT
WITHOUT HOODS/HOUSING,ONLY FOR REFERENCE
不使用防护外壳时芯件的开孔安装尺寸，仅供参考



4X M3 SCREW, RECOMMENDED
TIGHTENING TORQUE 0.5Nm
4X M3螺丝，推荐扭力矩为0.5Nm





NOTES:

1. TECHNICAL CHARACTERISTICS:
   INSULATION MATERIAL: PC
   RATED VOLTAGE: 500V
   RATED CURRENT: 16A
   INSULATION RESISTANCE: >=400MΩ
   RATED IMPULSE VOLTAGE: 6KV
   POLLUTION DEGREE: 3
   FLAMMABILITY: UL94V-0
   MATING CYCLES: 500 CYCLES
   WIRE RANGE: 0.5mm²~2.5mm² (AWG20-AWG14)
   CONTACT FINISH: SILVER PLATED
   CONTACT TYPE: DOUBLE SPRING CLAMP

注释：
1. 技术参数：
   绝缘材料： PC
   额定电压： 500V
   额定电流： 16A
   绝缘电阻： >=400MΩ
   脉冲电压： 6KV
   污染等级： 3
   阻燃等级： UL94V-0
   插拔次数： 500 次
   接线范围： 0.5mm²~2.5mm² (AWG20-AWG14)
   端子表面处理： 镀银
   接线类型： 双弹片连接

PART NUMBER 料号		PART DESCRIPTION 描述
T2040105201-000	HE-010-FSS	HE-010 FEMALE INSERT,DOUBLE SPRING CLAMP HE-010母插，双弹片

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
FINISH -

DWN DAVID WANG 24NOV2016
CHK CHRIS WANG 24NOV2016
APVD XIANG XU 24NOV2016
PRODUCT SPEC 108-137044
APPLICATION SPEC 114-137044
WEIGHT -

TE Connectivity

NAME HE-010-FSS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-T2040105201000	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:
T2040105201-000