

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

TAMPER-PROOF LABELS OVERVIEW



SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	D41400-000	MV-254254-10-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084
TN	C17219-000	TN-254254-10-9	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091


Quantity per roll: 10.000 PCs

Labels across: 3

Winding: outside

length of roll: 95,3 m



LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020		DATE		TE Connectivity	
SUBSTRATE		LABEL HEIGHT: ±0,3 [.012]		DIMENSIONS mm [INCHES]  TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		CHK S. Iser / 01.04.2020		DATE		TE Connectivity	
ADHESIVE		LABEL WIDTH: ±0,3 [.012]				APVD S. Iser / 01.04.2020		DATE		Name	
LINER		WEB WIDTH: ±0,8 [.031]				PRODUCT SPEC		DATE		Tamper-proof Label Size „254254“	
		VERTICAL REPEAT: ±0,8 [.031]*				APPLICATION SPEC		DATE			
		HORIZONTAL REPEAT: ±0,8 [.031]*				WEIGHT MV: 0,078 g TN: 0,065 g				SIZE	
		PRINT POSITIONING: ±0,8 [.031]*								CAGE CODE	
		LEFT MARGIN: ±0,4 [.016]		MATERIAL						DRAWING NO	
		QUANTITY: -0% +2%		FINISH						RESTRICTED TO	
		*NON ACCUMULATING		SEE TABLE						A3	
										C2290	
										C-TAMPER-PROOF	
										CUSTOMER DRAWING	
										SHEET 1 of 1	
										REV A1	

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[C17219-000](#)