

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

TAMPER-PROOF LABELS OVERVIEW


SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	C07219-000	MV-318097-10-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084
TN	D67328-000	TN-318097-10-9	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091

Quantity per roll: 10.000 PCs

Labels across: 1

Winding: outside

length of roll: 127 m



approx.
Ø
175-181
[6.890-7.126]

Ø
76,2
[3,00]

Color-appearance
on roll



TN
white



MV
silver

All dimensions in mm [inch]

labels are centered on the liner
as long as not declared separately

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020		DATE		TE Connectivity	
SUBSTRATE ADHESIVE LINER	LABEL HEIGHT:		±0,3 [.012]	DIMENSIONS mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - MATERIAL SEE TABLE FINISH	CHK S. Iser / 01.04.2020		DATE		Name Tamper-proof Label Size „318097“		
	LABEL WIDTH:		±0,3 [.012]		APVD S. Iser / 01.04.2020		DATE				
	WEB WIDTH:		±0,8 [.031]		PRODUCT SPEC		DATE				
	VERTICAL REPEAT:		±0,8 [.031]*		APPLICATION SPEC		DATE				
	HORIZONTAL REPEAT:		±0,8 [.031]*		WEIGHT MV: 0,038 g TN: 0,031 g		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
	PRINT POSITIONING:		±0,8 [.031]*				A3		C2290	C-TAMPER-PROOF	
	LEFT MARGIN:		±0,4 [.016]								
	QUANTITY:		-0% +2%								
			*NON ACCUMULATING				CUSTOMER DRAWING		SHEET 1 of 1		REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[C07219-000](#)