



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A	66	-	-	SEE SHEET 1	-	-	-


FEED TYPE
MECHANICAL






PNEUMATIC



SERVO
LATCH PLATE



CAM POSITIONS



ATLANTIC VERSION
Shown on sheets 1 of 4 & 2 of 4
(Pacific version shown on sheets 3 of 4 & 4 of 4)

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN: HOFFNER 13AUG2012		TE Connectivity	
mm		0 PLC ±.5		CHK: TELBIN 14AUG2012		Harrisburg, PA 17105-3608	
Ø		1 PLC ±0.13		APVD: TELBIN 14AUG2012		NAME: Ocean Side Feed Applicator	
FINISH		2 PLC ±0.013		PRODUCT SPEC		SIZE: CAGE CODE: DRAWING NO: 00779 ©=2151733	
MATERIAL		4 PLC ±.0030		APPLICATION SPEC		RESTRICTED TO: -	
-		-		WEIGHT		Customer Accessible Production Drawing	
-		-		SCALE: 1:1		SHEET 2 OF 4	
-		-		REV: B		SHEETS 3 & 4 ARE NOT REQUIRED FOR ATLANTIC VERSION	


DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2003

C


B

A


FEED TYPE MECHANICAL





PNEUMATIC



SERVO LATCH PLATE




CAM POSITIONS



PACIFIC VERSION
Shown on sheets 3 of 4 & 4 of 4
(Atlantic version shown on sheets 1 of 4 & 2 of 4)

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
A	66	-	-	SEE SHEET 1	-	-



DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.5 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±.5 ANGLES ±.0°30'		OWN: HOFFNER 13AUG2012 CHK: T.ELBIN 14AUG2012 APVD: T.ELBIN 14AUG2012	NAME: TE Connectivity Harrisburg, PA 17105-3608	
MATERIAL: -		FINISH: -		PRODUCT SPEC: -	APPLICATION SPEC: -	
WEIGHT: -		SCALE: 1:1		SHEET: 4	OF: 4	REV: B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2151733-2](#)