





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
P11		OBSOLETE 3-175444-6 ECR-20-007046	12NOV2020	PSJ	TM



- 注 記
- △ 面から2mmの範囲で測定
 - 2. 嵌合相手ハウジング型 174515, 175442, 917989, 917978
 - 3. 推奨取付ねじ : JIS B1115, B1122 クッピンねじ, なべ2種
呼び径3, 長さ6mm以下 (締付けトルク : 0.4N・m以下)
 - 4. 適用製品規格番号 : 108-5280, 108-5342
 - △ 回路番号
パワ-回路 ① ~ ⑬
シグナル回路 ⑭ ~ ⑳
 - △ コンタクト仕上識別マーク



- NOTES; △ MUST BE KEPT BETWEEN □ AND 2
- 2 THE MATING PLUG HSG. PART NUMBER; 174515, 175442, 917989, 917978
 - 3 RECOMMENDED MOUNTING SCREW; 3mmDIA, 6mmLENGTH(MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE; 0.4N・mMAX.)
 - 4 APPLICABLE PRODUCT SPEC NO. 108-5280, 108-5342
 - △ CIRCUIT NUMBER
POWER CIRCUIT NO. ① ~ ⑬
SIGNAL CIRCUIT NO. ⑭ ~ ⑳
 - △ MARKING FOR DISCERNMENT OF THE CONTACT FINISH

OBSOLETE

FJPI-7-175444-6	57	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8	14, 17, 18	24~26, 32, 34	GRAY 灰色	7-175444-6
FJPI-3-175444-6	53	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 13	2~5	28~24, 29~32	GRAY 灰色	3-175444-6
FJPI-6-175444-1	56	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8	-	19~22, 27~30	NATURAL 自然色	6-175444-1
FJPI-5-175444-9	55	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8	4, 6, 9, 12	26, 28, 29, 34	LIGHT GRAY 淡灰色	5-175444-9
FJPI-5-175444-1	55	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8	4, 6, 9, 12	26, 28, 29, 34	NATURAL 自然色	5-175444-1
FJPI-3-175444-2	53	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 13	2~5	28~24, 29~32	BLACK 黒色	3-175444-2
FJPI-2-175444-1	52	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 16	-	19~34	NATURAL 自然色	2-175444-1
FJPI-4-175444-6	54	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8	-	20, 24, 26~28, 32~34	GRAY 灰色	4-175444-6
FJPI-3-175444-1	53	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 13	2~5	28~24, 29~32	NATURAL 自然色	3-175444-1
FJPI-7-175444-6	7	TIN-LEAD	SELECTIVE GOLD × 8	14, 17, 18	24~26, 32, 34	GRAY 灰色	7-175444-6
FJPI-6-175444-1	6	TIN-LEAD	SELECTIVE GOLD × 8	-	19~22, 27~30	NATURAL 自然色	6-175444-1
FJPI-5-175444-9	5	TIN-LEAD	SELECTIVE GOLD × 8	4, 6, 9, 12	26, 28, 29, 34	LIGHT GRAY 淡灰色	5-175444-9
FJPI-5-175444-6	5	TIN-LEAD	SELECTIVE GOLD × 4	5, 6, 11, 12	-	GRAY 灰色	5-175444-6
FJPI-5-175444-2	5	TIN-LEAD	SELECTIVE GOLD × 8	4, 6, 9, 12	26, 28, 29, 34	BLACK 黒色	5-175444-2
FJPI-5-175444-1	5	TIN-LEAD	SELECTIVE GOLD × 8	4, 6, 9, 12	26, 28, 29, 34	NATURAL 自然色	5-175444-1
FJPI-4-175444-6	4	TIN-LEAD	SELECTIVE GOLD × 8	-	20, 24, 26~28, 32~34	GRAY 灰色	4-175444-6
FJPI-3-175444-6	3	TIN-LEAD	SELECTIVE GOLD × 13	2~5	28~24, 29~32	GRAY 灰色	3-175444-6
FJPI-3-175444-1	3	TIN-LEAD	SELECTIVE GOLD × 13	2~5	28~24, 29~32	NATURAL 自然色	3-175444-1
FJPI-2-175444-1	2	TIN-LEAD	SELECTIVE GOLD × 16	-	19~34	NATURAL 自然色	2-175444-1
FJPI-175444-9	0	PRE-TIN × 34	-	-	-	GRAY 灰色	175444-9
FJPI-175444-8	0	PRE-TIN × 34	-	-	-	ORANGE オレンジ色	175444-8
FJPI-175444-6	0	PRE-TIN × 34	-	-	-	GRAY 灰色	175444-6
FJPI-175444-5	0	PRE-TIN × 34	-	-	-	BLUE 青色	175444-5
FJPI-175444-3	8	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	34	-	NATURAL 自然色	175444-3
FJPI-175444-2	0	PRE-TIN × 34	-	-	-	BLACK 黒色	175444-2
FJPI-175444-1	0	PRE-TIN × 34	-	-	-	NATURAL 自然色	175444-1
PACKING INSTRUCTION NUMBER	△ MARKING マーキング	SOLDERING SIDE 半田付け面	CONTACT SIDE 接触部側	POWER CIRCUIT NO. パワ-回路	SIGNAL CIRCUIT NO. シグナル回路	COLOR	PART NUMBER 製品番号

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位 : 寸
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED
一般公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±

ANGLES
寸法

MATERIAL
材料

HOUSING : PBT
CONTACT : BRASS

FINISH
仕上

SEE TABLE

DWN
M. KADOSAKI

CHK
T. SHINOHARA

APVD
K. RESTUI

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

SIZE
寸法

CAGE CODE
19 g

DRAWING NO
00779

RESTRICTED TO

TE Connectivity

34POSITION CAP HOUSING ASS'Y
040/070 SERIES HYBRID I/O CONNECTOR

00779

175444

SCALE
2:1

SHEET
1 OF 1

REV
P11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[175444-6](#)