


注：

1. 材料 : HSG - 66ナイロン樹脂UL94V-0  
ポスト - 金メッキ付黄銅
2. 適用製品規格 : 108-5218
3. 嵌合相手製品型番 : P/N 176392

NOTES;

1. MATERIAL; HOUSING - 66 NYLON (UL94V-0)  
POST - GOLD-PLT BRASS
2. PRODUCT SPEC.; 108-5218
3. APPLICABLE RECEPTACLE; P/N 176392



RECOMMENDABLE P.C.B. BOARD LAYOUT  
**推奨基板寸法**  
 (板厚 0.8-1.6)  
 (PCB THK:0.8-1.6)

F	変 更	FJ00- 1400-97	2.0	7/9	16/9
E	キンク変更	FJ00- 1343-97	E.C J.T	9/8	9/8
D	キンク変更	J-1780	T.F S.K	12/1	9/8
C	キンク変更	J-1486	S.K J.T	9/8	9/8
B	変 更	J-1013	T.F S.K	11/2	9/8
A	変 更	J-12466	T.F S.K	6/2	9/8
O	作 成	J-12272	T.F S.K	2/1	9/8
LTR	REVISION RECORD		DR	CHK	DAT

Copyright © 19 年  
■ 平工一・エム・ビ一株式会社

Copyright ©19\_\_  
AMP (Japan), LTD.  
ALL RIGHTS RESERVED.

WIRE RANGE	INSULATION DIA
mm <sup>2</sup> C.AWG - )	mmφ
MATERIAL SEE NOTE 1 注1参照	FINISH SEE NOTE 1 注1参照
DR. 1/31/'90 T. FURUYA	DE. 1/31/'90 T. FURUYA
CHK. 2/1/'90 S. KIKUCHI	APP. <i>S. Kikuchi</i> 2/1/'90

BLUE 青色						
	2-176394-6	6	10	13.8	7.2	13.0
NATURAL 自然色 (白色) (WHITE)						
	176394-6	6	10	13.8	7.2	13.0
	↑ -5	5	8	11.8	5.2	11.0
	-4	4	6	9.8	3.2	9.0
	↓ -3	3	4	7.8	—	7.0
176394-2	2	2	5.8	—	5.0	
COLOR 色	P/N 型番	Pos. 極数	A	B	C	D

# AMP

AMP (JAPAN), LTD.  
Tokyo, Japan

NAME				ボックス仕様バストヘッダーアッセンブリ (水平型)			
金メッキ				タイプ (AMP CT コネクタ 2mmピッチ)			
				POST HEASER ASS'Y (BOX-H)			
				GOLD PLT TYPE (AMP CT CONNECTOR 2mm PITCH)			
GENERAL TOLERANCE		SIZE	LOC	NUMBER			
0<≦ 10 : ±0.2		B	J	C-176394			
10<≦ 30 : ±0.25							
30<≦ 100 : ±0.3		SCALE		REV.		SHEET	
ANGLES : ±3°		5 - 1		F		1 OF 1	

CUSTOMER DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[176394-4](#)