



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION .19
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
AJ	16						
		✓	✓		A	REDWN & REV PER AJ-2637	5-6-88
					B	REV PER AJ-3649	2-16-89



1. FOR USE WITH: RG-405/U, .086 DIA SEMI-RIGID CABLE
2. USE CRIMPING TOOL: 59980-1
USE PNEUMATIC TOOL: 58318-1
3. SEE I.S.: 6788 & 9351
4. .320 MIN LENGTH OF STRAIGHT CABLE REQUIRED TO APPLY TO CONNECTOR
- 5 STAINLESS STEEL PER ASTM-A-582
- 6 BERYLLIUM COPPER PER QQ-C-530
- 7 SILICONE RUBBER PER ZZ-R-765
- 8 PTFE PER MIL-P-19468
- 9 BRASS PER MIL-C-50
- 10 SEALANT
- 11 GOLD PL PER MIL-G-45204
- 12 NICKEL PL PER QQ-N-290
- 13 PASSIVATED PER QQ-P-35
14. FREQUENCY RANGE: 0 TO 26.5 GHZ



221812-1			
PART NO			
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± 3 PLC DEC ±.005 ANGLES ±		AMP AMP INCORPORATED Harrisburg, Pa. 17105	
MATERIAL 5 THRU 10	DR R. RUTH 5-6-88	NAME PLUG, WEATHERPROOF, SERIES SMA	
	CHK M. SNEED 5-9-88		
FINISH 11 THRU 13	APPD M. WALMSLEY 5-10-88	SIZE C FSCM NO 00779 DRAWING NO 221812-1	
	APPD R. RUTH 5-10-88		
APPLICATION SPEC		SCALE 5:1	
WEIGHT		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[221812-1](#)