



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.


© COPYRIGHT 1962

REVISIONS				
P	F	LTR	DESCRIPTION	DATE
✓		F	REV-REDWN	CB2-515
				5/1/83

1. FOR USE WITH: *1-12 / 1799-3*
2. CRIMPING TOOL: *612-1*
3. SEE *1.S. 1799-3*.



RECOMMENDED STRIP LENGTH



RECOMMENDED PANEL CUT-OUT

ITEM	QTY	DESCRIPTION	PART NO
7	1	FERRULE	328666
6	1	GASKET	2-329106-1
5	1	LOCK WASHER	329632
4	1	JAM NUT	329631
3	1	GASKET	329633
2	1	CRIMP END ASSY	50793-4
1	1	JACK ASSY, BHD	329603

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS \pm ANGLES \pm

MATERIAL

FINISH

CONTRACT NO

DR

CHK

APPD

APPD

DSGN APPD

OTHER APPD

AMPAMP INCORPORATED
Harrisburg, Pa. 17105

NAME

CONNECTOR, COAXIAL, RF
JACK, BHD, SERIES BNC

SIZE

A

FSCM NO

00779

DRAWING NO

*2-329092-1*SCALE *1/16"*

SHEET

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-329092-1](#)