



© 1961 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP
PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

REVISIONS

ZONE	LTR	DESCRIPTION	DATE	APPROVED
B		REDRAWN & UPDATED PC-5561	10-17-69	Jme
C		BUTT WAS PARALLEL PC-5575	5-8-70	Jme
C1		REV PER ECR 05-013140	11-21-05	JE/m



BUSHING

SLEEVE ASSEMBLY

WIRE SPLICE

FOR .040 TO .050 WIRE INSULATION DIA.

QTY	DESCRIPTION	PART NO.	MATERIAL & FINISH
2	BUSHING	21434-1	TEFLON(MIL-P-19468) COLOR: NATURAL
1	WIRE SPLICE	324369	COPPER(QQ-C-576) GOLD PL(MIL-G-45204)TYPE II .00005 MIN THK OVER NICKEL PL(QQ-N-290).00003 MIN THK.
1	SLEEVE ASSY	324329	INSULATION: TEFLON(MIL-P-19468) COLOR: NAT. RING: ALUMINUM(QQ-A-250/I) COLOR: YELLOW
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON: DECIMALS ± .008 ANGLES ± 5°			
MATERIAL		CONTRACT NO. 11	AMP INCORPORATED HARRISBURG, PENNSYLVANIA
SEE TABLE		DR. 10-8-69 CHK 10-17-69 APPD 10-20-69 RE 10-20-69 DEGN APPD OTHER APPD	NAME WIRE SPLICE POST INSULATED STRATO-THERM MOISTURE SEAL-BUTT WIRE SIZE: 26-24
		SIZE B	CODE IDENT NO. 00779
		SCALE NTS	NUMBER 324370
			SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[324370](#)