



©1965 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

AMP 332416  
UNPUBLISHED COPY NOT TO BE REPRODUCED NOR PUBLISHED WITHOUT WRITTEN PERMISSION OF AMP INCORPORATED.

REVISIONS				
ZONE	LTR	DESCRIPTION	DATE	APPROVED
	A	.240 DIA WAS .200 DIA F4481		
	B	CH'G'D MATERIAL & FINISH	3/18/66	RHW
	B	REV PER ECN P-5194	6/27/66	RHW
	C	CH'G'D MAT'L SPEC PC-5514	7-20-67	RHW



NOTE:  
1. TIN PL (MIL-T-10727) TYPE I

UNLESS OTHERWISE SPECIFIED DIM. ARE IN INCHES. TOLERANCES ON: DECIMALS ± .008 ANGLES ± 5°		CONTRACT NO. 11-9-65		<b>AMP</b> AMP INCORPORATED HARRISBURG, PENNSYLVANIA	
MATERIAL CARBON STEEL AISI TYPE 1008 OR 1010		NAME IGNITION SYSTEM TERMINAL		NUMBER 332416	
HEAT TREAT #		SIZE B		CODE IDENT NO. 00779	
FINISH NOTE 1		OTHER APPD		SCALE 4-1	
LOC PRINT/DIST G14C		WT CALC ACTUAL		SHEET 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[332416](#)