

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2009

© COPYRIGHT 2009


BY -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
E3		ECR-09-022009	18NOV2009	SR	OD
E4		REVISED PER ECR-17-014013	10JAN2018	SRG	MKO
E5		ECR-20-000801	17JAN2020	QY	JB


PN 0-1 AS SHOWN




PN 0-2 AS SHOWN




PN 0-2 AS SHOWN




PN 0-4 AS SHOWN




PN 0-5 AS SHOWN




PN 0-1 AS SHOWN




PN 0-2 AS SHOWN




PN 0-4 AS SHOWN



PN 0-5 AS SHOWN



5



NOTES:

1 PACKAGING QUANTITY: 5 PIECES PER BOX

MATERIAL: HOUSING: ALUMINUM DIE CAST ALLOY

SEALS: NEOPRENE

2

SURFACE: VARNISH GREY

ALUMINUM OXIDE + VARNISH BLACK

3

VARNISH ON THE INSIDE NOT NECESSARY

OBSOLETE	OBSOLETE	OBSOLETE	OBSOLETE	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM	NOTES
2	2	2	2	INSULATING TAPE	COROPLAST TYP 303		GREY RAL7001	7	PVC SOFT
1	1	1	1	PROFILE SEAL	NEOPRENE		BLACK	6	
	2			CLIP BOLT	STAINLESS STEEL	BLANK		5	
1				HOOD HD	ALU. ALLOY		GREY RAL7001	4	
	1			HOOD HD	ALU. ALLOY	ALUMINUM OXID	BLACK	3	
		1		HOOD HD	ALU. ALLOY		GREY RAL7001	2	
			1	HOOD HD	ALU. ALLOY		GREY RAL7001	1	
0-5	0-4	0-2	0-1	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM	NOTES
				HD-15.ST0.1.M25.G					
				HD-15.STS.1.M25.G					
				HD-K.15.STS.1.M25.G					
				HD-15.ST					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN V. GLUMM 18NOV2009

CHK -

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0° PLC ±

1° PLC ±

2° PLC ±

3° PLC ±

4° PLC ±

ANGLES ±°

FINISH -

material_2

finish_spec_2

NAME

CONNECTOR HOUSING ASS'Y

SERIES HD.15 METRIC THREAD

SIZE A2

CAGE CODE 00779

DRAWING NO C-1106414

RESTRICTED TO

SCALE 1:1

SHEET 1 OF 1

REV E5

1471-9 (3/13)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1106414-4](#)