

© —TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	10	INITIAL RELEASE	11FEB2020	GK	AK

NOTES: —

1. CHARACTERS: —
0–9, A–Z, +, –, /,~, ≡
0, 1, 6 & 9 FOLLOWED BY A FULL STOP.
HEIGHT 2.6 – 2.9 mm
TOLERANCE (AXIAL) ±0.75
(ROTATIONAL) ±5°
CHEVRON CUT MARKERS: —
CHARACTERS TO BE CENTRALLY DISPOSED
ON MARKER FACE AND IN THE ATTITUDE
SHOWN RELATIVE TO CHEVRON.

2. MARKER LENGTHS (DIMENSION 'A'): —
WITH SINGLE MARK 4.00 – 4.75
WITH DOUBLE MARK 6.75 – 7.25

DIM 'A'

140°

A

CHEVRON CUT

0.95

4.85

C

STRAIGHT CUT

DIM 'A'

A

C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2020 GOPALAKRISHNA H V		STE TE Connectivity						
DIMENSIONS: mm		CHK 11FEB2020 ALAN KEAN								
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 11FEB2020 ALAN KEAN		NAME MARKER Z TYPE SIZE 11 STRAIGHT / CHEVRON CUT —					
	0 PLC ± —		PRODUCT SPEC							
	1 PLC ± 0.2		—							
	2 PLC ± —		APPLICATION SPEC							
3 PLC ± —		—		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO			
4 PLC ± —		ANGLES ± —		A300779		C=1601A0004	—			
MATERIAL PVC 3.1 – 2.8g/250mm		FINISH —		WEIGHT —		CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	REV 10

1470–19 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EJ0341-000](#)